


3M™ Molded Assembly

2 mm x 2 mm

2M Series



- Available in multiple sizes
- Sockets mate with standard 2 mm × 2 mm headers and plugs
- Molded-in strain relief
- See Regulatory Information Appendix (RIA) for chemical compliance information

Date Modified: January 23, 2008

TS-2150-C
Sheet 1 of 2

Physical

Connector:

Technical Specification: TS-0525 for 2 mm × 2 mm Molded-On Socket
TS-2151 for 2 mm × 2 mm Molded-On PCB

Cable:

Technical Specification: TS-0452 for 1mm Flat Ribbon Cable

Electrical

Voltage Rating: 30 V


Environmental

Temperature Rating: -20°C to +105°C

3M™ Molded Assembly

2 mm x 2 mm

2M Series



Left Connector


Right Connector

Note: A fan-out assembly, with multiple connectors on one end, requires a drawing submittal and review.

Length (Dim A) Tolerance		
Min.	Max.	Tol.
1.7	10.0	± 0.3
10.0	20.0	± 0.5
20.0	40.0	± 0.6
40.0	120.0	± 1.0
120.0		± 2.0

Available Options															
Connector/Pos.	6	8	10	12	16	20	22	24	26	30	34	36	40	44	50
Socket	x	x	x		x	x	x	x	x	x	x		x	x	x
PCB	x	x	x	x	x	x			x	x		x	x	x	x
Cable	x	x	x	x	x	x	x	x	x	x	x	x	x	x	x
Cable/Pos.	6	8	10	12	16	20	22	24	26	30	34	36	40	44	50

Note: If "Keying" is required, mark the circuit(s) to key.



Ordering Information

2M XX XX - XXX - XXXX - XXX.X - XX - XX - XX - X

Connector Types

(Left and Right)

Socket, Low Profile (.29")

AA = no Centerbump, no Latching Ear

AB = Centerbump, no Latching Ear

AC = no Centerbump, with Latching Ear (See Note 1)

AD = Centerbump, with Latching Ear (See Note 1)

PCB, 2-Row

BD = Matte Sn Plating, Straight Solder Tail

Number of Cable Conductors

Cable Product Series

28 AWG

3625 = Stranded, PVC

Left Right

Connector Feature Options

0 = No Keying Required

4 = Keying Required, specify position(s)

Assembly Length

Tip-to-Tip inches

(Dim A in inches)

Example:

001.7 = 1.7" Min

Marking

0 = No Marking

1 = Label - Date Code

2 = Inkstamp - Date Code

Left Right Centerbump Orientation

Options

0 = None

1 = Inside

2 = Outside

Connector Orientation

Options

(Left and Right)

AB = Up-Up

AD = Up-Down

CB = Down-Up

CD = Down-Down

Notes: 1. Latching ear option is required for mating with the 3M™ Latch/Eject Header 2 mm, 1552 Series

2. (RIA E1 & C1 apply for all cables and connectors listed)

TS-2150-C
Sheet 2 of 2