

IQMS-910, -912 SERIES MEMS OSCILLATORS

ISSUE 3; 1 NOVEMBER 2010 - RoHS 2002/95/EC

Description

- LVPECL output low jitter MEMS oscillator in a plastic package
- Factory programmable for a fast lead time
- Stock parts listed at the beginning of this chapter

Frequency Ranges

- 1 to 220MHz
- 220 to 800MHz (contact IQD sales offices)

Output Compatibility & Load

- LVPECL
- Output load 50Ω terminated to $V_S - 2.0V$
- Output Level 0.8V pk-pk typical

Supply Voltages

- 3.3V IQMS-910
- 2.5V IQMS-912

Frequency Stabilities

- $\pm 10\text{ppm}$, $\pm 15\text{ppm}$ $\pm 20\text{ppm}$, $\pm 25\text{ppm}$, $\pm 50\text{ppm}$ over the operating temperature range (inclusive of tolerance, supply voltage variation, load variation)
Note: $\pm 10\text{ppm}$ only available over 0 to 70°C

Operating Temperature Ranges

- 0 to 70°C
- -20 to 70°C
- -40 to 85°C

Storage Temperature Range

- -65 to 150°C

Tri-state Operation (TS option)

- Logic '1' to pad 1 ($\geq 70\%V_S$) enables oscillator output
- Logic '0' to pad 1 ($\leq 30\%V_S$) disables oscillator output; when disabled the oscillator output goes to the high impedance state
- No connection to pad 1 enables oscillator output

Standby (ST option)

- Logic '1' to pad 1 ($\geq 70\%V_S$) enables oscillator output
- Logic '0' to pad 1 ($\leq 30\%V_S$) disables oscillator output; when disabled the oscillator output goes to the high impedance state, oscillation stops
- No connection to pad 1 enables oscillator output
- Standby Current: 25μA typical @3.3V
15μA typical @2.5V

RMS Period Jitter @ 200MHz

- 1.3ps typical




RMS Phase Jitter @ 200MHz, BW 1MHz to 20MHz

- 0.7ps typical

Ageing

- $\pm 1\text{ppm}$ typ in 1st year at 25°C

Outline (mm)




Underside View

Pad Connections

1. TS / ST
2. N/C
3. GND
4. Output +
5. Output -
6. +V_S

Solder Pad Layout



Environmental

- Shock: MIL-STD-883F, Method 2002
- Vibration: MIL-STD-883F, Method 2007
- Temperature Cycle: MIL-STD-883F, Method 1010
- Solderability: MIL-STD-883F, Method 2003
- MSL level 1

Packaging

- Loose in bulk pack, 100pcs per bag
- Tape and reel in accordance with EIA-481-D, 1kpcs per reel (please see pages 372 & 373)

Ordering Information (*minimum required)

- Frequency*
- Model*
- Output
- Frequency Stability (over operating temperature range)*
- Operating Temperature Range*
- Supply Voltage
- TS/ST Option

Example

- 40.00MHz IQMS-910
LVPECL $\pm 25\text{ppm}$ -40 to 85C 3.3V ST




Electrical Specifications - maximum limiting values

Frequency Range	Frequency Stability	Supply Voltage	Supply Current (no load)	Rise Time (tr) (20-80%)	Fall Time (tf) (80-20%)	Duty Cycle	Model Number
1.0 to 220.0MHz	$\pm 10\text{ppm}$ $\pm 15\text{ppm}$ $\pm 20\text{ppm}$ $\pm 25\text{ppm}$ $\pm 50\text{ppm}$	3.3V $\pm 10\%$	74mA	300ps	300ps	45/55%	IQMS-910
		2.5V $\pm 10\%$	71mA				IQMS-912

Note: For other frequency/specification combinations, please contact our sales offices

Output Waveform



Test Circuit

