

Identification tags for cable bundle, thermal transfer

TIPTAG PU - UV-stabilised Tiptags, Polyurethane

These Tiptags are designed for use in identifying wire and cable bundles in electronics and general cabling environments. The labels are applied to cables and harness assemblies with cable ties, and are also suitable for retrofit purposes. Secured to bundles using Cable Ties up to T50R width maximum.

Printers: TT4000+ and TT430

Ribbon: TTRC+

Software: TagPrint Pro


Features and Benefits

- Identification tags TIPTAG, Polyurethane
- Very tough and flexible material
- For bigger cable bundles and wires
- For cable ties up to 4.7 mm width
- Print with TT4000+ and TT430 for best results
- Delivery on reel, perforated
- Flame retardant
- Weather resistant
- Abrasion resistant
- Good resistance to chemicals
- Special lengths and colours available on request



The printed mark has a tattoo-like permanency.

MATERIAL	Polyurethane (PUR)
Operating Temperature	-65 °C to +120 °C, intermittent 150 °C
Flammability	Self extinguishing, UL94 V0 (3 mm)
Recommended Ribbon Type	TTRC+



TYPE	Length (L)	Width (W)	Pack Cont.	Colour	Article-No.
TTAGPU11X65WH	65.0	11.0	190 pcs.	White (WH)	556-25012
TTAGPU11X65YE	65.0	11.0	190 pcs.	Yellow (YE)	556-25019
TTAGPU15X65WH	65.0	15.0	190 pcs.	White (WH)	556-25007
TTAGPU15X65YE	65.0	15.0	190 pcs.	Yellow (YE)	556-25011
TTAGPU11X100WH	100.0	11.0	125 pcs.	White (WH)	556-25021
TTAGPU11X100YE	100.0	11.0	125 pcs.	Yellow (YE)	556-25020
TTAGPU15X100WH	100.0	15.0	125 pcs.	White (WH)	556-25006
TTAGPU15X100YE	100.0	15.0	125 pcs.	Yellow (YE)	556-25010

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.