



Ref. Certif. No.

SI-4571IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC**CB TEST CERTIFICATE****CERTIFICAT D'ESSAI OC**Product
Produit

Power Supply for Medical use

Name and address of the applicant
Nom et adresse du demandeurFRIWO Gerätebau GmbH
Von-Liebig-Strasse 11, D-48346 Ostbevern, GermanyName and address of the manufacturer
Nom et adresse du fabricantFRIWO Gerätebau GmbH
Von-Liebig-Strasse 11, D-48346 Ostbevern, GermanyName and address of the factory
Nom et adresse de l'usineFRIWO Gerätebau GmbH
Von-Liebig-Strasse 11, D-48346 Ostbevern, Germany*Note: When more than one factory, please report on page 2*
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2ème page Additional Information on page 2Ratings and principal characteristics
Valeurs nominales et caractéristiques principalesInput: 100-240 Vac; 50-60 Hz; 350-150 mA, Class II
Output: Additional information on page 2Trademark (if any)
Marque de fabrique (si elle existe)

FWGB

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

/

Model / Type Ref.
Ref. De typeFW7555M/xx, FW7555MZ/05
Additional information on page 2.Additional information (if necessary may also be reported
on page 2)
Les informations complémentaires (si nécessaire, peuvent
être indiqués sur la 2ème pageThe risk management requirements of the standard were not
addressed. Additional Information on page 2A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60601-1:2005 (3rd Ed.) + A1:2012

As shown in the Test Report Ref. No. which forms
part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

T223-0002/15, dated 2015-01-07

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**Slovenski institut za kakovost in meroslovje
Slovenian Institute of Quality and Metrology
Tržaška c. 2, SI-1000 Ljubljana, Slovenia
Product Certification Body is accredited by Slovenian Accreditation, Reg. No.: CP-001

Date: 2015-01-07

Signature: Igor Likar

Name and address of the factory

- 1) FRIWO Gerätebau GmbH
Von-Liebig-Strasse 11, D-48346 Ostbevern, Germany
- 2) TABEMAX SP J
ULICA BETONOWA 1, PL-86-005 BIALE BLOTA, POLAND
- 3) TABER
Ul. Oliwiana 24, PL-85-461 Bydgoszcz, Poland
- 4) NOVIL Sp. z.o.o.
Miszewko, Sloneczna 8, PL-80-297 Banino, Poland
- 5) Golden Regent Electronics Industrial Ltd.
Huangjinghu Management District
CN-523500 Qishi Town, Dongguan; Guangdong, PR China
- 6) PEI-Genesis
651 WINKS LN
BENSALEM PA US-19020-5994, USA
- 7) Roofer Technology (Shenzhen) Co., Ltd.
Roofer Building, GeXia Industrial Area,
Sanlian Village, Dalang Road, Longhua Town, Shenzhen,
PR China

Ratings and principal characteristics:

Input: 100-240 Vac; 50-60 Hz; 350-150 mA; Class II

Output:

Model number	Output voltage	Output current
FW7555M/05	5 Vdc	2400 mA
FW7555MZ/05	5 Vdc	2400 mA
FW7555MZ/05 (Revision No. 1)	5 Vdc	2400 mA
FW7555M/06	6 Vdc	2100 mA
FW7555M/08	7,5 Vdc	1700 mA
FW7555M/09	9 Vdc	1500 mA
FW7555M/12	12 Vdc	1250 mA
FW7555M/15	15 Vdc	1000 mA
FW7555M/18	18 Vdc	840 mA
FW7555M/24	24 Vdc	625 mA

Additional information (if necessary)**Information complémentaire (si nécessaire)**

This CB test certificate substitutes previously issued CB test certificate No. SI-4438, dated 2014-11-19, due to update of test report.

Date: 2015-01-07

Signature: Igor Likar