

Coupler connector - SF-5EP1N8AF4DU - 1605519

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Coupler connector, straight, Screw locking, M23, Number of positions: 5+PE, Type of contact: Male connector, Crimp connection, Shielded: Yes, Cable diameter: 7.5 mm...14 mm

The figure shows the 8-pos. (4+3+PE) product version



Key commercial data

Packing unit	20 pc
GTIN	 4 046356 253376
Weight per Piece (excluding packing)	92.19 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Note	Order information Order crimp contacts 6 x Ø 2 mm separately
Type of locking	Screw locking
Coding	N
Contact connection method	Crimp connection
Type of contacts	Male connector
Number of positions	6
Contact diameter of power contacts	2 mm
Nominal current per power contact at 25°C	30 A
Contact diameter of signal contacts	2 mm
Nominal current per signal contact at 25°C	30 A
Conductor entry	7.5 mm ... 14 mm

Ambient conditions

Ambient temperature	-20 °C ... 125 °C
Degree of protection	IP67

Coupler connector - SF-5EP1N8AF4DU - 1605519

Technical data

Material

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 66
Gasket and O-ring material	FPM

Specifications according to DIN EN 61984:2001

Installation height max.	3000 m
Nominal / operating voltage of power contacts	630 V
Rated surge voltage of power contacts	6 kV
Surge voltage category of power contacts	III
Pollution degree of power contacts	3
Nominal / operating voltage of signal contacts	630 V
Rated surge voltage of signal contacts	6 kV
Surge voltage category of signal contacts	III
Pollution degree of signal contacts	3

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Coupler connector - SF-5EP1N8AF4DU - 1605519

Approvals

Approvals

cUL Recognized / UL Recognized / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

cUL Recognized

mm ² /AWG/kcmil	4
Nominal current I _N	15 A
Nominal voltage U _N	600 V


UL Recognized

mm ² /AWG/kcmil	4
Nominal current I _N	25 A
Nominal voltage U _N	600 V


cULus Recognized

Drawings

Schematic diagram



Diagram



Coupler connector - SF-5EP1N8AF4DU - 1605519

Dimensioned drawing

