


LP2K12105ED

TeSys K reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 12 A - 48 V DC coil



Main

| | |
|---|--|
| Range | TeSys |
| Product name | TeSys K |
| Product or component type | Reversing contactor |
| Device short name | LP2K |
| Contactor application | Motor control Resistive load |
| Utilisation category | AC-1 AC-3 AC-4 |
| Device presentation | Preassembled with reversing power busbar |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | 690 V AC 50/60 Hz for power circuit <= 690 V AC 50/60 Hz for signalling circuit |
| [Ie] rated operational current | 20 A (<= 50 °C) at <= 440 V AC AC-1 for power circuit 16 A (<= 70 °C) at 690 V AC AC-1 for power circuit 12 A at <= 440 V AC AC-3 for power circuit |
| Motor power kW | 3 kW at 220...230 V AC 50/60 Hz 4 kW at 480 V AC 50/60 Hz 4 kW at 500...600 V AC 50/60 Hz 4 kW at 660...690 V AC 50/60 Hz 5.5 kW at 380...415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz |
| Control circuit type | DC standard |
| Control circuit voltage | 48 V DC |
| Auxiliary contact composition | 1 NO |
| [Uimp] rated impulse withstand voltage | 8 kV |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 20 A at <= 50 °C for power circuit 10 A at <= 50 °C for signalling circuit |
| Irms rated making capacity | 110 A AC for signalling circuit conforming to IEC 60947 144 A AC for power circuit conforming to NF C 63-110 144 A AC for power circuit conforming to IEC 60947 |
| Rated breaking capacity | 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 80 A 1 s signalling circuit 90 A 500 ms signalling circuit 110 A 100 ms signalling circuit 115 A <= 50 °C 1 s power circuit 105 A <= 50 °C 5 s power circuit 100 A <= 50 °C 10 s power circuit 75 A <= 50 °C 30 s power circuit 55 A <= 50 °C 1 min power circuit 50 A <= 50 °C 3 min power circuit 25 A <= 50 °C >= 15 s power circuit |
| Associated fuse rating | 25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|-------------------------------|---|
| Average impedance | 3 mOhm at 50 Hz - lth 20 A for power circuit |
| [Ui] rated insulation voltage | 690 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit conforming to UL 508 690 V for signalling circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-5-1 600 V for signalling circuit conforming to UL 508 600 V for power circuit conforming to CSA C22.2 No 14 600 V for signalling circuit conforming to CSA C22.2 No 14 |
| Electrical durability | 0.3 Mcycles 20 A AC-1 at $U_e \leq 440$ V 1.3 Mcycles 12 A AC-3 at $U_e \leq 440$ V |
| Interlocking type | Mechanical |
| Mounting support | Plate Rail |
| Standards | BS 5424 IEC 60947 NF C 63-110 VDE 0660 |
| Product certifications | CSA UL |
| Connections - terminals | Solder pins 1.5 x 0.9 mm |
| Operating time | 10 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 5 Mcycles |
| Operating rate | 3600 cyc/h |

Complementary

| | |
|--------------------------------|---|
| Control circuit voltage limits | 0.8...1.15 U_c at ≤ 50 °C operational 0.1...0.75 U_c at ≤ 50 °C drop-out |
| Inrush power in W | 3 W at 20 °C |
| Hold-in power consumption in W | 3 W at 20 °C |
| Heat dissipation | 3 W |
| Auxiliary contacts type | Type instantaneous 1 NO |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non overlap distance | 0.5 mm |
| Insulation resistance | > 10 MOhm for signalling circuit |

Environment

| | |
|---------------------------------------|---|
| IP degree of protection | IP2x conforming to VDE 0106 |
| Protective treatment | TC conforming to IEC 60068 TC conforming to DIN 50016 |
| Ambient air temperature for operation | -25...50 °C |
| Ambient air temperature for storage | -50...80 °C |
| Operating altitude | 2000 m without derating in temperature |
| Flame retardance | V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102 |
| Mechanical robustness | Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor opened, on X axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on X axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis 10 Gn for 11 ms IEC 60068-2-27 |

| | |
|----------------|---------|
| Height | 58 mm |
| Width | 90 mm |
| Depth | 57 mm |
| Product weight | 0.48 kg |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS | Compliant - since 0706 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |