



### Main

Range of product	Harmony 9001K
Product or component type	Illuminated pushbutton
Bezel material	Chromium plated metal
Mounting diameter	30 mm
Shape of signaling unit head	Octagonal
Light source	Incandescent (bulb included)
Bulb base	BA 9s
[Us] rated supply voltage	230 V AC/DC
Contacts type and composition	1 C/O
Connections - terminals	Screw clamp terminals , 1 x 0.22...2 x 1.5 mm <sup>2</sup> conforming to IEC 60947-1

### Complementary

Tightening torque	0.8 N.m conforming to IEC 60947-1
Mechanical durability	5000000 cycles
Operating position	Any position
[Ie] rated operational current	3 A at 240 V AC-15 , A600-Q600
[Ui] rated insulation voltage	250 V pollution degree 3 conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	2.5 kV conforming to IEC 60947-1
Contacts material	Silver alloy contacts
Contacts operation	Standard
Positive opening	Without
Short circuit protection	10 A cartridge fuse conforming to IEC 60947-5-1
[Icm] rated short-circuit making capacity	$\leq 0.1$ kA at 600 V DC-13 $\leq 0.27$ kA at 250 V DC-13 $\leq 0.55$ kA at 125 V DC-13 $\leq 12$ kA at 600 V AC-15 , 7200 VA $\leq 15$ kA at 480 V AC-15 , 7200 VA $\leq 30$ kA at 240 V AC-15 , 7200 VA $\leq 60$ kA at 120 V AC-15 , 7200 VA
Rated breaking capacity	$\leq 0.1$ kA at 600 V DC-13 $\leq 0.27$ kA at 250 V DC-13 $\leq 0.55$ kA at 125 V DC-13 $\leq 1.2$ kA at 600 V AC-15 , 720 VA $\leq 1.5$ kA at 480 V AC-15 , 720 VA $\leq 3$ kA at 240 V AC-15 , 720 VA $\leq 6$ kA at 120 V AC-15 , 720 VA
Product weight	0.25 kg

### Environment

Standards	CSA C22-2 No 14 EN/IEC 60947-5-1 IEC 60947-1 IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C

Vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Class of protection against electric shock	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529 IP66 conforming to NF C 20-010