
103945

- 1 CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2 USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3 THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103660
- 6 ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7 MATERIAL— HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK PINS: PHOS. BRONZE
- 8 FINISH— PINS: .000015 GOLD IN THE CONTACT AREA, .000050—.000100 BRIGHT TIN—LEAD ON THE TERMINATION AREA, OVER .000050 NICKEL.
- 9 FINISH— PINS: .000015 GOLD IN THE CONTACT AREA, .000050—.000100 BRIGHT TIN ON THE TERMINATION AREA, OVER .000050 NICKEL.
- 10 PRELIMINARY PART — NOT RELEASED FOR PRODUCTION.
- 11 FINISH— PINS: .000015 GOLD IN THE CONTACT AREA, .000050—.000100 MATTE TIN ON THE TERMINATION AREA, OVER .000050 NICKEL.
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

12 SUPERSEDED BY 5-103945-8

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.BROWN 26JUL00 CHK K.WRIGHT 26JUL00 APVD K.WRIGHT 26JUL00		 TE Connectivity			
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, POLARIZED, W/ LATCH WINDOWS, FOR #22-#26 AWG WIRE SIZE, STRIP FORM			
MATERIAL		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026 WEIGHT -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		FINISH		A2	00779	C-103945	-
SEE TABLE		CUSTOMER DRAWING			SCALE	SHEET	REV
					4:1	1 of 1	M2