


160 - 250kg

Industrial Castors Series 3470

Housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, dustguard, wheel axle with nut
 Drawings of plate fittings see on page 38-39
 Load capacity tested according EN 12532



| | Wheel diameter [mm] | Width of Tread [mm] | Size of Plate [mm] | Plate hole centres [mm] | Plate hole [mm] | Offset [mm] | Overall height [mm] | Load capacity [kg] | Express / On Stock | Order number | EAN Code |
|---------------------------------------|---------------------|---------------------|--------------------|-------------------------|-----------------|-------------|---------------------|--------------------|--------------------|---------------------------|---------------|
| Swivel Castors | | | | | | | | | | | |
| | 100 | 34 | 105 x 85 | 80/77 x 60 | 9 | 41 | 128 | 160 | | 3470UFR100P62 blue | 4031582304411 |
| | 125 | 40 | 105 x 85 | 80/77 x 60 | 9 | 40 | 155 | 250 | | 3470UFR125P62 blue | 4031582304442 |
| Fixed Castors | | | | | | | | | | Order number | EAN Code |
| | 100 | 34 | 103 x 85 | 80/77 x 60 | 9 | | 128 | 160 | | 3478UFR100P62 blue | 4031582306958 |
| | 125 | 40 | 103 x 85 | 80/77 x 60 | 9 | | 155 | 250 | | 3478UFR125P62 blue | 4031582306972 |
| Swivel Castors with total lock | | | | | | | | | | Order number | EAN Code |
| | 100 | 34 | 105 x 85 | 80/77 x 60 | 9 | 41 | 128 | 160 | | 3477UFR100P62 blue | 4031582305890 |
| | 125 | 40 | 105 x 85 | 80/77 x 60 | 9 | 40 | 155 | 250 | | 3477UFR125P62 blue | 4031582305920 |

Wheel: UFR blue
 Wheel centre: Polyamide, black, Tread: Elastic-tyre, blue, non-marking, without threadguards, roller bearing

Directional lock
 Directional locking castors are available in all sizes.