

Printed-circuit board connector - MSTBO 2,5/4-6 ST SET KMGY - 2713764

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Kit consisting of COMBICON header and screw connectors for 6 x 4 positions (24-pos.), color: Light gray



Why buy this product



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 914493
Weight per Piece (excluding packing)	55.31 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Product type	Printed circuit board housing
Approval	CSA
	VDE report with production monitoring
	IECEE CB Scheme
	UL Recognized
	cUL Recognized
	CCA
	EAC
	cULus Recognized
Rated voltage (IEC)	320
Rated current (IEC)	12
Mounting type	Soldering
Number of positions	4
Pitch	5 mm

Printed-circuit board connector - MSTBO 2,5/4-6 ST SET KMGY - 2713764

Technical data

Levels	single-level
Type of locking	Without

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27260701
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

CSA / VDE Gutachten mit Fertigungsüberwachung / IECCEB Scheme / UL Recognized / cUL Recognized / CCA / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

Printed-circuit board connector - MSTBO 2,5/4-6 ST SET KMGY - 2713764

Approvals

CSA		
	B	D
mm ² /AWG/kcmil	28-12	28-12
Nominal current I _N	10 A	10 A
Nominal voltage U _N	300 V	300 V

VDE Gutachten mit Fertigungsüberwachung	
Nominal current I _N	8 A
Nominal voltage U _N	250 V

IECEE CB Scheme	
Nominal current I _N	8 A
Nominal voltage U _N	250 V

UL Recognized		
	B	D
mm ² /AWG/kcmil	30-12	30-12
Nominal current I _N	15 A	10 A
Nominal voltage U _N	300 V	300 V

cUL Recognized		
	B	D
mm ² /AWG/kcmil	30-12	30-12
Nominal current I _N	15 A	10 A
Nominal voltage U _N	300 V	300 V

Printed-circuit board connector - MSTBO 2,5/4-6 ST SET KMGY - 2713764

Approvals

CCA	
Nominal current I _N	8 A
Nominal voltage U _N	250 V

EAC



Accessories

Accessories

Coding element


Coding section - CR MSTBO-G1 - 2199618

Coding section




Drawings

Schematic diagram



Schematic diagram



Pin assignment right

Pin assignment left