




# Terminal blocks spring connection

double deck

Standard

 DIN 3

End stop	th. 9,0 mm	<b>BADL</b>	V0	<b>0199 408.02</b>
End stop	th. 9,1 mm	<b>BAMH</b>	V0	<b>0194 836.01</b>
End stop	th. 9,1 mm	<b>BAMH</b>	V2	<b>0114 836.00</b>
<i>Other end stops: See Accessories section</i>				
Rail	 35 x 7,5 x 1	<b>PR3Z2</b>		<b>0174 300.17</b>
Rail	 35 x 15 x 2,3	<b>PR4</b>		<b>0168 500.12</b>
Rail	 35 x 15 x 1,5	<b>PR5</b>		<b>0168 700.22</b>
<i>Other rails: See Accessories section</i>				
<i>Other accessories: See Accessories section</i>				

## Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.


One wire per spring.

Terminal block body material is UL 94 V0.

\*Entrelec spring connection terminal blocks comply with IEC 947-1 standard for 2.5 mm<sup>2</sup> rated wire size. Our spring terminal blocks can also be connected to 4 mm<sup>2</sup> solid wires.

## Accessories

- 1 End section grey
- 2 Test plug black
- 3 Jumper bar orange  
IP20 - 24 A




4 Vertical jumper bar



**R** See section on markers  
Marking method



## D 2,5/5.D2.L

Spacing 5 mm +0,05 .197"



Standard terminal blocks spacing 5 mm.



Color	Type	Part number
Grey	 <b>D 2,5/5.D2.L</b>	<b>0290 161.00</b>
Blue	 <b>D 2,5/5.D2.N.L</b>	<b>0290 163.02</b>

Color	Type	Part number

## Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Solid wire	0,12-4 * mm <sup>2</sup>		26-12 AWG	26-12 AWG
Stranded wire	0,12-2,5 mm <sup>2</sup>		26-12 AWG	26-12 AWG
With isolated ferrule	0,5-2,5 mm <sup>2</sup>			

## Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Solid wire				
Stranded wire				
With isolated ferrule				

Voltage			
Rated	500 V	300 V	300 V
Pulse	6 kV		
Pollution degree	3		

Voltage			
Rated			
Pulse			
Pollution degree			

Current			
Rated	20 A	20 A	20 A

Current			
Rated			


Wire size			
Rated / Gauge	2,5 mm <sup>2</sup> / A2	12 AWG	12 AWG
Wire stripping length	Recommended screwdriver	Recommended torque	Protection
9,5 mm	3,5 mm		IP 20
.37"	.14"		NEMA 1

Wire size			
Rated / Gauge			
Wire stripping length	Recommended screwdriver	Recommended torque	Protection

Type	Part number
<b>FED5.D.L</b> V0 th. 2,5 mm	<b>0291 441.26</b>
<b>FC2</b> V2 DIA. 2,0 mm	<b>0007 865.26</b>
<b>BJDL5.2</b> V0 2 poles	<b>0291 102.23</b>
<b>BJDL5.3</b> V0 3 poles	<b>0291 103.24</b>
<b>BJDL5.4</b> V0 4 poles	<b>0291 104.25</b>
<b>BJDL5.5</b> V0 5 poles	<b>0291 105.26</b>
<b>BJDL5.6</b> V0 6 poles	<b>0291 106.27</b>
<b>BJDL5.7</b> V0 7 poles	<b>0291 107.20</b>
<b>BJDL5.8</b> V0 8 poles	<b>0291 108.01</b>
<b>BJDL5.9</b> V0 9 poles	<b>0291 109.02</b>
<b>BJDL5.10</b> V0 10 poles	<b>0291 110.26</b>
<b>ITVE.L</b>	<b>0291 349.11</b>

Type	Part number

Mounting of the vertical jumper bar between decks (**ITVE.L** item 4)



On top: RC510 (6) or RPC (20)  
On sides: RC55 (5)