




LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
					K3	REVISED PER ECO-11-004587		11MAR11	RK	HMR



RECOMMENDED HOLE LAYOUT

		3.984	3.900	39	40	9-103323-0
OBSOLETE		3.884	3.800	38	39	8-103328-9
OBSOLETE		3.784	3.700	37	38	8-103328-8
OBSOLETE		3.684	3.600	36	37	8-103328-7
		3.584	3.500	35	36	8-103328-6
OBSOLETE		3.484	3.400	34	35	8-103328-5
OBSOLETE		3.384	3.300	33	34	8-103328-4
OBSOLETE		3.284	3.200	32	33	8-103328-3
OBSOLETE		3.184	3.100	31	32	8-103328-2
OBSOLETE		3.084	3.000	30	31	8-103328-1
OBSOLETE		2.984	2.900	29	30	8-103328-0
OBSOLETE		2.884	2.800	28	29	7-103323-9
OBSOLETE		2.784	2.700	27	28	7-103323-8
OBSOLETE		2.684	2.600	26	27	7-103323-7
OBSOLETE		2.584	2.500	25	26	7-103323-6
OBSOLETE		2.484	2.400	24	25	7-103323-5
OBSOLETE		2.384	2.300	23	24	7-103323-4
OBSOLETE		2.284	2.200	22	23	7-103323-3
OBSOLETE		2.184	2.100	21	22	7-103323-2
OBSOLETE		2.084	2.000	20	21	7-103323-1
		1.984	1.900	19	20	7-103323-0
OBSOLETE		1.884	1.800	18	19	6-103323-9
OBSOLETE		1.784	1.700	17	18	6-103323-8
OBSOLETE		1.684	1.600	16	17	6-103323-7
OBSOLETE		1.584	1.500	15	16	6-103323-6
OBSOLETE		1.484	1.400	14	15	6-103323-5
OBSOLETE		1.384	1.300	13	14	6-103323-4
OBSOLETE		1.284	1.200	12	13	6-103323-3
OBSOLETE		1.184	1.100	11	12	6-103323-2
OBSOLETE		1.084	1.000	10	11	6-103323-1
		.984	.900	9	10	6-103323-0
OBSOLETE		.884	.800	8	9	5-103323-9
OBSOLETE		.784	.700	7	8	5-103323-8
OBSOLETE		.684	.600	6	7	5-103323-7
OBSOLETE		.584	.500	5	6	5-103323-6
		.484	.400	4	5	5-103323-5
		.384	.300	3	4	5-103323-4
OBSOLETE		.284	.200	2	3	5-103323-3
OBSOLETE		.184	.100	1	2	5-103323-2
OBSOLETE		.084	—	—	1	5-103323-1
PLATING	C	B	A	NO OF POSN	PART NUMBER	

			.184	.100	1	2	4-103323-2
			3.984	3.900	39	40	4-103323-1
			3.984	3.900	39	40	4-103323-0
	OBSOLETE		3.884	3.800	38	39	3-103323-9
	OBSOLETE		3.784	3.700	37	38	3-103323-8
	OBSOLETE		3.684	3.600	36	37	3-103323-7
	SUPERSEDED		3.584	3.500	35	36	3-103323-6
	OBSOLETE		3.484	3.400	34	35	3-103323-5
	OBSOLETE		3.384	3.300	33	34	3-103323-4
	OBSOLETE		3.284	3.200	32	33	3-103323-3
	OBSOLETE		3.184	3.100	31	32	3-103323-2
	OBSOLETE		3.084	3.000	30	31	3-103323-1
	OBSOLETE		2.984	2.900	29	30	3-103323-0
	OBSOLETE		2.884	2.800	28	29	2-103323-9
	OBSOLETE		2.784	2.700	27	28	2-103323-8
	OBSOLETE		2.684	2.600	26	27	2-103323-7
	OBSOLETE		2.584	2.500	25	26	2-103323-6
	OBSOLETE		2.484	2.400	24	25	2-103323-5
	OBSOLETE		2.384	2.300	23	24	2-103323-4
	OBSOLETE		2.284	2.200	22	23	2-103323-3
	OBSOLETE		2.184	2.100	21	22	2-103323-2
	OBSOLETE		2.084	2.000	20	21	2-103323-1
			1.984	1.900	19	20	2-103323-0
	OBSOLETE		1.884	1.800	18	19	1-103323-9
	OBSOLETE		1.784	1.700	17	18	1-103323-8
	OBSOLETE		1.684	1.600	16	17	1-103323-7
			1.584	1.500	15	16	1-103323-6
	OBSOLETE		1.484	1.400	14	15	1-103323-5
	OBSOLETE		1.384	1.300	13	14	1-103323-4
	OBSOLETE		1.284	1.200	12	13	1-103323-3
	OBSOLETE		1.184	1.100	11	12	1-103323-2
	OBSOLETE		1.084	1.000	10	11	1-103323-1
			.984	.900	9	10	1-103323-0
			.884	.800	8	9	103323-9
	OBSOLETE		.784	.700	7	8	103323-8
			.684	.600	6	7	103323-7
			.584	.500	5	6	103323-6
	SUPERSEDED		.484	.400	4	5	103323-5
	SUPERSEDED		.384	.300	3	4	103323-4
			.284	.200	2	3	103323-3
			.184	.100	1	2	103323-2
	OBSOLETE		.084	—	—	1	103323-1
	PLATING	C	B	A	NO OF POSN	PART NUMBER	

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
2. BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
3. .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
4. .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
5. PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
6. HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK. POSTS: PHOS BRONZE
7. .000100-.000200 MATTE TIN OVER .000050 NICKEL.
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL

6

DWN J.MARTINELLI

CHK JOHN KNITTLE

APVD B.FLINCHBAUGH

NAME

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

160CT92

23NOV92

23NOV92

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE 4:1

SHEET 1 OF 1

REV K3

TE Connectivity

HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 , RIGHT ANGLE, WITH .025 SQUARE POSTS

A100779

103323