

Interface module - VIP-2/PT/HD15SUB/F - 2904272

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with push-in connection and high density D-SUB miniature socket strip, for mounting on NS 35, no. of pos.: 15

The figure shows a 44-pos. version, with pin strip



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 814812
Weight per Piece (excluding packing)	114.0 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	46.9 mm
Height	72.1 mm
Depth	46.6 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC/DC
Max. perm. current (per branch)	1 A
Number of positions	15
Status display	No
Mounting position	any

Interface module - VIP-2/PT/HD15SUB/F - 2904272

Technical data

General

Standards/regulations	EN 50178
Rated surge voltage	1.2 kV
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Push-in connection
Number of positions	15
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	High-density D-SUB socket strip
Number of positions	15

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

Interface module - VIP-2/PT/HD15SUB/F - 2904272

Classifications

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	105 V

UL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	125 V

Interface module - VIP-2/PT/HD15SUB/F - 2904272

Approvals


cUL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	125 V

EAC


cULus Recognized

Drawings

Circuit diagram



Schematic diagram



Universal circuit diagram