



ENGLISH

Datasheet

Stock No: 236-026

RS Pro Green Lens For Use With Xenon Beacons



Product Details

14W Xenon Beacon

A high performance range suitable for 12/24V applications requiring maximum visibility e.g. construction, utility or agricultural vehicles

Vibration protected circuits

Reverse polarity protection

Supply voltage: 12/24Vdc

Current consumption: 2A / 1A @ 12/24V

Single or Double Flash operation possible

Flash Rate: 125 fpm

IP56 rated

Operating temperature range: -30°C to +50°C

Magnetic versions are rated to 70mph

Note

Lens must be purchased separately.

DIN-mount stem only suitable for DIN mounting types.

Large cage guard only suitable for Three-point mounting type.

Approvals

ECE65 where Amber or Blue lens are used

Supplied with

Bulb

Xenon Strobe



ENGLISH

Specifications

For Use With

Xenon Beacons

Colour

Green