

VIP-2/SC/PDM-2/16

Order No.: 2315256



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2315256>

VARIOFACE module, with two equipotential busbars (P1, P2) for potential distribution, for mounting on NS 35/7.5 or NS 32. Module width: 50.0 mm



Commercial data	
EAN	4046356313360
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.1211 KG
Catalog page information	Page 296 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
09/02/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data	
Nominal voltage U_N	250 V AC/DC
Maximum total current per potential	15 A
Potential connections	Per potential (P1, P2) 2 power/8 distributor terminal blocks
Width	50 mm

Height	50 mm
Depth	65.5 mm
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	III

Connection data, supply

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M 3

Connection data, distribution

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M 3

Certificates / Approvals



Certification CUL, UL

CUL



Comments	Output
Nominal voltage U_N	250 V
Nominal current I_N	12 A
AWG/kcmil	30-12
Comments	Input
Nominal voltage U_N	250 V
Nominal current I_N	12 A
AWG/kcmil	30-10

UL

Comments	Output
Nominal voltage U_N	250 V
Nominal current I_N	12 A
AWG/kcmil	30-12
Comments	Input
Nominal voltage U_N	250 V
Nominal current I_N	12 A
AWG/kcmil	30-10

Drawings

Circuit diagram



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford Shropshire TF7 4PG,GB
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



© 2009 Phoenix Contact
Technical modifications reserved;