

BJMI5D-10

ABB contact for United
States of America



General Information

Extended Product Type:	BJMI5D-10
Product ID:	1SNA176740R1100
EAN:	3472591767407
Catalog Description:	BJMI5D-10 Jumper Bars
Long Description:	BJMI5D-10 - Jumper Bars - 10 poles - - 5mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591767407
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	12.00 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.12000 kg
Package Level 1 EAN:	3472591767407
Package Level 2 Units:	500 piece
Package Level 2 Width:	175 mm
Package Level 2 Height:	130 mm
Package Level 2 Length:	227 mm
Package Level 3 Units:	90000 piece

Additional Information

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	Simplified model, composed of a bar prepunched to the spacing of the blocks, and of captive screws and spacers. This accessory can be used for connecting blocks which are consecutive or not: in this case remove the screw and spacer which are not required.
Product Main Type:	BJMI
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 24 A
Spacing:	5 mm

Sub-Function: Assembled jumper bar
Sub-Function 2: Screw

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225002C1007
GOST Certificate: 1SND161005A1104

Classifications

ETIM 4.0: EC000489 - Cross-connector for terminal block
ETIM 5.0: EC000489 - Cross-connector for terminal block
Object Classification Code: X

