

# Product Information

## 2040UAP125R05-28

EAN 4031582300109

Swivel castor, Frame made of pressed steel, yellow zinc plated, precision ball bearing in swivel head and wheel, housing cover made of synthetic plastics.

Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing, solid plug fitting

### Option:

This castor is also in electric conductive version available. (grey non-marking). Please replace UAP with XSX when ordering..



Wheel diameter	125 mm
Width of Tread	32 mm
Bolt-Ø	28 mm
Bolt length	45 mm
Offset	35 mm
Swivel Interference	195 mm
Overall height	158 mm
Temperature	- 30 / + 80 °C
Standard	EN 12531
Weight	1.042 kg
Dynamic Load capacity	150 kg
Static Load capacity	300 kg
Swivel Radius	97.5 mm
Hardness of tread	D 40 Shore

