

Cable - CABLE-50/4FLK14/ 3,0M/YUC - 2314668

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled round cable with a 50-pos. molded socket strip and four 14-pos. socket strips, for splitting 32 channels into 4 x 8 channels, number of positions: 50/ 4 x 14, the cable is suitable for the ADV551 and ADV151 boards. Length of cable: 3.0 m



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 147309
Weight per Piece (excluding packing)	603.1 g
Custom tariff number	85444290
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

General

Nominal voltage U_N	30 V DC
Max. current carrying capacity per path	500 mA (Up to 55°C ambient temperature)
Max. conductor resistance	0.16 Ω /m
Length of cable	3 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	11 mm
Shielding	no
Outer sheath, material	PVC
External sheath, color	Gray RAL 7035

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Cable - CABLE-50/4FLK14/ 3,0M/YUC - 2314668

Technical data

Environmental conditions

Flame resistance	IEC 60332-1
Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	Against occasional splashes

Connector, module side

Number of positions	14
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	4

Connector, controller side

Number of positions	50
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	1

Connection data

Connection method	Screw connection
Torque	0.5 Nm

Supported controller

Controller	YOKOGAWA CENTUM CS3000R3
- suitable I/O card	ADV151
	ADV551
Controller	YOKOGAWA STARDOM
- suitable I/O card	NFDV151
	NFDV551

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27249205

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

Cable - CABLE-50/4FLK14/ 3,0M/YUC - 2314668

Classifications

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Cable - CABLE-50/4FLK14/ 3,0M/YUC - 2314668

Connection diagram

50-pos. connector to the I/O card	4 x 14-pos. connector to the module	Wire color
50	Byte 0	1 black
49		3 brown
48		5 red
47		7 orange
46		9 yellow
45		11 green
44		13 blue
43		15 violet
42		44 gray
41		39 white
40	Byte 1	17 white-black
39		19 white-brown
38		21 white-red
37		23 white-orange
36		25 white-yellow
35		27 white-green
34		29 white-blue
33		31 white-violet
32		43 white-gray
31		37 brown-black
30	Byte 2	2 brown-red
29		4 brown-orange
28		6 brown-yellow
27		8 brown-green
26		10 brown-blue
25		12 brown-violet
24		14 brown-gray
23		16 brown-white
22		42 green-black
21		36 green-brown
20	Byte 3	18 green-red
19		20 green-orange
18		22 green-blue
17		24 green-violet
16		26 green-gray
15		28 green-white
14		30 yellow-black
13		32 yellow-brown
12		41 yellow-red
11		34 yellow-orange