

Datasheet

7mm, Shackle, Nylon Multi-Pole Breaker Lockout

RS Stock number [411-0577](#)



Description:

- Single device that can be used with most major multi-pole breakers that employ a tie bar.
- Versatile device that is compatible with most name-brand manufacturers, such as GE, ITE, Sylvania, Cutler-Hammer, Challenger, Bryant, Siemens, Square D, and General Switch Company.
- Easy to use and install.

Material:

- Clamp and Housing made of molded Glass-filled Nylon
- Stainless Steel screw with over molded Glass-filled Nylon thumbscrew.
- Colour: Housing – Red (PMS 1805C)
- Colour: Thumbscrew - Black
- UL Rating: 94-HB

Chemical	°C	Chemical	°C
Acetone	25	Petroleum	25
Acetone	60	Turpentine oil	25
Chlorine, chlorine water	25	Turpentine substitute (white spirit)	25
Fuel, engine: Gasoline (normal & premium grade)	85	Trichloroethane 1,1,1	45
Lubrication oil: gear oil	< 120	Lubricating oil: HD engine oils, hydraulic oils, transformer oils	< 120
Fuel, engine: M15 mixture (15% methanol)	70	Water (including seawater)	25
Methanol	25	Water (including seawater), chlorinated (<0,5 mg/l)	80

Temperature Range

- Glass-filled Nylon: -20° to 120°C (0° to 250°F)

Chemical Resistance

All approved chemicals listed are based on the manufactures specified chemical resistance chart for plastic material only.

"A"	–	2.100" [53.3mm]
"B"	–	2.450" [62.2mm]
"C"	–	0.300" [7.6mm]
"D"	–	0.610" [15.5mm]
"E"	–	1.250" [31.8mm]
"F"	–	0.312" [7.9mm] MAX

