

Data sheet

6GK5795-1TR10-0AA6

Product type designation

IWLAN terminating resistor TI795-1R RSMA Male
 SIMATIC NET R-SMA MALE TERMINATION IMPEDANCE TI795-1R, 50 OHM 2.4 AND 5GHZ, IP65, 0..6GHZ TERMINATOR 50 OHM
 1 PACKAGING UNIT = 3 PCS



Electrical data	
Number of electrical connections	1
Type of electrical connection	R-SMA male
Transmission frequency	0 ... 6 GHz
Impedance	50 Ω
Return loss / minimum	25 dB
Permitted ambient conditions	
Ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Protection class IP	IP65
Design, dimensions and weight	
Diameter	9 mm
Length	15 mm
Net weight	5 g
Standards, specifications, approvals	

Certificate of suitability • RoHS conformity	Yes
Further Information / Internet Links	
Internet-Link • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support last modified:	http://www.siemens.com/snst http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com 11.02.2016