

Patch cable - VS-RJ45-RJ45-94P-0,5 - 1418028

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Patch cable, CAT5e, 4-pair, shielded, line, assembled at both ends with straight RJ45/IP20 heads, length: 0.5 m



Key commercial data

| | |
|--------------------------------------|--|
| Packing unit | 1 pc |
| GTIN |  4 046356 534284 |
| Weight per Piece (excluding packing) | 46.3 g |
| Custom tariff number | 85444210 |
| Country of origin | China |

Technical data

Dimensions

| | |
|-----------------|-------|
| Length of cable | 0.5 m |
|-----------------|-------|

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP20 |
|----------------------|------|

General data

| | |
|----------------------|--|
| Number of positions | 8 |
| Signal type/category | Ethernet CAT5 (IEC 11801:2002), 0.1 Gbps |
| | Ethernet CAT5e (TIA 568B:2001), 0.1 Gbps |

Characteristics head 1

| | |
|--|---------------------------|
| Head type | Plug Straight RJ45 / IP20 |
| No. of positions (pin connector pattern) | 8 (8) |
| Color | black |
| Material (component) | CuSn (Contact) |
| | Ni/Au (Contact surface) |
| | PC (Contact carriers) |
| | TPU (Grip) |

Patch cable - VS-RJ45-RJ45-94P-0,5 - 1418028

Technical data

Characteristics head 1

| | |
|----------|-----|
| Shielded | Yes |
|----------|-----|

Characteristics head 2

| | |
|--|---------------------------|
| Head type | Plug Straight RJ45 / IP20 |
| No. of positions (pin connector pattern) | 8 (8) |
| Color | black |
| Material (component) | CuSn (Contact) |
| | Ni/Au (Contact surface) |
| | PC (Contact carriers) |
| | TPU (Grip) |
| Shielded | Yes |

Cable

| | |
|---|--|
| Cable type | Ethernet, flexible, CAT5e |
| Cable type (abbreviation) | 94B |
| UL AWM style | 20963 (80°C/30 V) |
| Signal type/category | Ethernet CAT5 (IEC 11801:2002), 0.1 Gbps |
| | Ethernet CAT5e (TIA 568B:2001), 0.1 Gbps |
| Cable structure | 4x2xAWG26/7; SF/UTP |
| Conductor cross section | 4x 2x 0.14 mm ² |
| AWG signal line | 26 |
| Conductor structure signal line | 7x 0.16 mm |
| Core diameter including insulation | 0.98 mm |
| Thickness, insulation | 0.25 mm |
| Wire colors | white/blue-blue, white/orange-orange, white/green-green, white/brown-brown |
| Twisted pairs | 2 cores to the pair |
| Overall twist | 4 pairs |
| Shielding | Aluminum-coated foil, tinned copper braided shield |
| Optical shield covering | 70 % |
| External sheath, color | water blue RAL 5021 |
| Outer sheath thickness | 1 mm |
| External cable diameter D | 6.4 mm ±0.2 mm |
| Smallest bending radius, fixed installation | 25.6 mm |
| Smallest bending radius, movable installation | 51.2 mm |
| Tensile strength short-term/long-term | ≤ 100 N |
| Cable weight | 47 kg/km |
| Outer sheath, material | PUR |
| Material conductor insulation | PE |
| Conductor material | Bare Cu litz wires |
| Insulation resistance | ≥ 500 MΩ*km |
| Loop resistance | ≤ 290 Ω (per kilometer) |

Patch cable - VS-RJ45-RJ45-94P-0,5 - 1418028

Technical data

Cable

| | |
|---|---|
| Working capacitance | 48 nF (At 1 kHz) |
| Wave impedance | 100 Ω ±5 Ω (at 100 MHz) |
| Signal runtime | 5.3 ns/m |
| Coupling resistance | ≤ 100.00 mΩ/m (At 10 MHz) |
| Nominal voltage, cable | ≤ 100 V |
| | 300 V (Outer cable sheath) |
| Test voltage Core/Core | 700 V (50 Hz, 1 min.) |
| Test voltage Core/Shield | 700 V (50 Hz, 1 min.) |
| Flame resistance | IEC 60332-1-2 |
| Halogen-free | According to IEC 60754-1 |
| Resistance to oil | in accordance with DIN EN 60811-2-1 |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |
| | -20 °C ... 80 °C (cable, flexible installation) |
| Ambient temperature (installation) | -20 °C ... 80 °C |
| Ambient temperature (storage/transport) | -20 °C ... 80 °C |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250591 |
| eCl@ss 4.1 | 27240409 |
| eCl@ss 5.0 | 27259207 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 19170107 |
| eCl@ss 7.0 | 19170112 |
| eCl@ss 8.0 | 19170112 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001262 |
| ETIM 3.0 | EC001262 |
| ETIM 4.0 | EC000830 |
| ETIM 5.0 | EC000830 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121609 |
| UNSPSC 7.0901 | 26121609 |
| UNSPSC 11 | 26121609 |
| UNSPSC 12.01 | 26121609 |
| UNSPSC 13.2 | 26121609 |

Drawings


Patch cable - VS-RJ45-RJ45-94P-0,5 - 1418028

Cable cross section



Ethernet, flexible, CAT5e [94B]

Dimensioned drawing



RJ45 connector, IP20

Circuit diagram

