







TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PBT
 COLOR: WHITE
 CONTACT MATERIAL: COPPER ALLOYS
 CONTACT TYPE: STAMPED
 CONTACT PLATING: SELECTIVE GOLD
 SHIELDING: BRASS Ni PLATED
 QUALITY CLASS: 1500 MATING CYCLES


ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 FLAMABILITY RATING: UL94-V0
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 1.5 A max
 WORKING VOLTAGE: 30V
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 750V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX

STANDARD
 CERTIFIED: E323964 / MODEL NUMBER 614-x350

SOLDERING
 WAVE PROCESS ONLY

PACKAGING
 TRAY

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 WÜRTH ELEKTRONIK	
G							
F							
E	08-NOV-11	CURRENT RATING	GG				
D	22-JUN-11	CURRENT RATING	GG				
C	19-NOV-09	STANDARD	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: DUAL USB TYPE A VERTICAL	SIZE A4
B	05-DEC-07	MODIFICATIONS	EC		SCALE:		
A	03-NOV-06	PDF	JP		SHEET: 1/1	WERI PART NO: 614 008 235 023	
REV	DATE	FILE	BY		DRAW: PEARL		