


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN)


METRIC




THIRD ANGLE
PROJECTION




- 1) PER PEZZI IN NASTRO
VEDERE DISEGNO 160433
(FOR STRIP VERSION SEE DWG. 160433).
 - 2) CONFEZIONAMENTO IN ACCORDO ALLA
SPECIFICA AMP 107-20201.
(PACKAGING ACCORDING TO AMP SPEC. 107-20201)
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



SEZIONE A-A
(SECTION A-A)



SEZIONE B-B
(SECTION B-B)



OBSOLETE △ 3	STAGNATO (TIN PLATED)	BRONZO FOSF. (PHOS. BRONZE)	5-160493-8	J
	PRE NICHELATO (PRE-NICKEL PL.)	ACCIAIO (STEEL)	5-160493-4	J
OBSOLETE	STAGNATO (TIN PLATED)	OTTONE (BRASS)	5-160493-2	J
	NUDO (PLAIN)	OTTONE (BRASS)	5-160493-1	J
	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (TE P/N)	REV

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY TE INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. TE PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO

(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

± 0.3

± 2°

DIAM. ISOLANTE
(INS. DIA. RANGE)

2.3-3.3

RANGO FILO
(WIRE RANGE) mm2

0.5-1.5

SCALA
(SCALE)

4:1

TE TE Connectivity

DESCRIZIONE
(DESCRIPTION) FASTON Connector,
.187" sr. REC. CONTACT
(LOOSE PIECE VERSION)

LOC. SIZE NUMERO
(DWG NO)

I A3 C-160493

REV. J2

FOGLIO
(SHEET) 1 OF 1

J2	ECR-10-022530	KK	11FEB11
J1	REVISED PER ECO-09-022178	KK	25SEP09
J	FIRST EMISSION ET00-0198-01	CH. Y.	27 JUL 2001
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (OR)	APP. DATA (APP.)