

## Classic ECO A55

CLECO A55 240V 28W B22 SV1

0023480



### Range features

- 1:1 replacement of Incandescent A55 lamp
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable
- Average rated life 1500hrs or 2000hrs - up to two times more average life compared to incandescent lamps



### PRODUCT OVERVIEW

Light colour	828 Homelight
Technology	Halogen
Ordering number	0023480
Average life (Rated) (h)	2000
Energy class	D
Lamp shape	GLS A55
Lamp finish	Clear
Dimmable	Yes
Cap/Base	B22
Type	Classic 'A' Shape
EAN code	5410288234809
CRI (Ra)	100
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	240

## Classic ECO A55

CLECO A55 240V 28W B22 SV1

0023480

### DATA TABLE

#### General data

<b>Ordering number</b>	0023480
<b>Technology</b>	Halogen
<b>Average life (Rated) (h)</b>	2000
<b>Average life (Nominal) (h)</b>	2000
<b>Energy class</b>	D
<b>Energy saving lamp</b>	No
<b>Lamp shape</b>	GLS A55
<b>Lamp finish</b>	Clear
<b>Dimmable</b>	Yes
<b>Cap/Base</b>	B22
<b>Type</b>	Classic 'A' Shape
<b>EAN code</b>	5410288234809
<b>E-number SE</b>	8355571
<b>Long description</b>	1:1 replacement of Incandescent A55 lamp. More efficient - more savings. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable. Average rated life 1500hrs or 2000hrs - up to two times more average life compared to incandescent lamps
<b>Product name</b>	CLECO A55 240V 28W B22 SV1
<b>Lamp mercury content (mg)</b>	0
<b>Starting time (max) (s)</b>	0.01
<b>Warm-up time to 60% of full light (max) (s)</b>	Instant full light
<b>Control gear required</b>	No
<b>Fixture rating</b>	Open
<b>IEC Reference</b>	IEC 60357
<b>IEC Reference 2</b>	IEC 60432-2
<b>Intended purpose</b>	General lighting
<b>No. of switching cycles before premature failure (min)</b>	> 8000
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	10
<b>Optimal operating condition (°C)</b>	25

## Classic ECO A55

CLECO A55 240V 28W B22 SV1

0023480

### Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	370

### Electrical data

kWh per 1000 hours burning time	28
Watt (Rated) (W)	28
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	240
Lamp power factor	1

### Physical data

Weight (kg)	0.03
Lamp Length (mm) - C/L	98.5
Max. Lamp Diameter (mm) - D	56
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	9.60 x 5.50 x 5.50
Inner package dimensions (L x W x H) (cm)	28.00 x 11.00 x 10.00
Inner package net weight (kg)	0.30
Outer package dimensions (L x W x H) (cm)	59.00 x 30.50 x 22.50


## Classic ECO A55

CLECO A55 240V 28W B22 SV1


0023480

### TECHNICAL DRAWINGS

Classic ECO A55



B22



### ENERGY LABEL

