








RECOMMENDED HOLE LAYOUT

			64.01 [2.520]	66.04 [2.600]	24	25	7-103634-4
OBSOLETE 			61.47 [2.420]	63.50 [2.500]	23	24	7-103634-3
			58.93 [2.320]	60.96 [2.400]	22	23	7-103634-2
			56.39 [2.220]	58.42 [2.300]	21	22	7-103634-1
			53.85 [2.120]	55.88 [2.200]	20	21	7-103634-0
			51.31 [2.020]	53.34 [2.100]	19	20	6-103634-9
			48.77 [1.920]	50.80 [2.000]	18	19	6-103634-8
			46.23 [1.820]	48.26 [1.900]	17	18	6-103634-7
			43.69 [1.720]	45.72 [1.800]	16	17	6-103634-6
			41.15 [1.620]	43.18 [1.700]	15	16	6-103634-5
			38.61 [1.520]	40.64 [1.600]	14	15	6-103634-4
			36.07 [1.420]	38.10 [1.500]	13	14	6-103634-3
			33.53 [1.320]	35.56 [1.400]	12	13	6-103634-2
			30.99 [1.220]	33.02 [1.300]	11	12	6-103634-1
			28.45 [1.120]	30.48 [1.200]	10	11	6-103634-0
			25.91 [1.020]	27.94 [1.100]	9	10	5-103634-9
			23.37 [.920]	25.40 [1.000]	8	9	5-103634-8
			20.83 [.820]	22.86 [.900]	7	8	5-103634-7
			18.29 [.720]	20.32 [.800]	6	7	5-103634-6
			15.75 [.620]	17.78 [.700]	5	6	5-103634-5
		13.21 [.520]	15.24 [.600]	4	5	5-103634-4	
		10.67 [.420]	12.70 [.500]	3	4	5-103634-3	
		8.13 [.320]	10.16 [.400]	2	3	5-103634-2	
		5.59 [.220]	7.62 [.300]	1	2	5-103634-1	
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.	

1. .000100 BRIGHT TIN—LEAD OVER .000050 NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
4. ON ASSEMBLIES WITH FOUR OR MORE POSITIONS,
TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS,
ONE POLARIZATION SLOT.
5. .000100 BRIGHT TIN OVER .000050 NICKEL.
6. PRELIMINARY PART — NOT RELEASED FOR PRODUCTION.
7. .000100 MATTE TIN OVER .000050 NICKEL.
8. HIGH TEMPERATURE CONFIGURATION
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	5	30.99 [1.220]	33.02 [1.300]	1 1	12	3-103634-4	
		25.91 [1.020]	27.94 [1.100]	9	10	3-103634-3	
		23.37 [.920]	25.40 [1.000]	8	9	3-103634-2	
		18.29 [.720]	20.32 [.800]	6	7	3-103634-1	
		15.75 [.620]	17.78 [.700]	5	6	3-103634-0	
		5.59 [.220]	7.62 [.300]	1	2	2-103634-9	
		41.15 [1.620]	43.18 [1.700]	15	16	2-103634-8	
		13.21 [.520]	15.24 [.600]	4	5	2-103634-7	
		10.67 [.420]	12.70 [.500]	3	4	2-103634-6	
		8.13 [.320]	10.16 [.400]	2	3	2-103634-5	
9	SUPERCEDED BY 7-103634-4		64.01 [2.520]	66.04 [2.600]	24	25	2-103634-4
	OBSOLETE 9	61.47 [2.420]	63.50 [2.500]	23	24	2-103634-3	
		58.93 [2.320]	60.96 [2.400]	22	23	2-103634-2	
		56.39 [2.220]	58.42 [2.300]	21	22	2-103634-1	
		53.85 [2.120]	55.88 [2.200]	20	21	2-103634-0	
		51.31 [2.020]	53.34 [2.100]	19	20	1-103634-9	
		48.77 [1.920]	50.80 [2.000]	18	19	1-103634-8	
		46.23 [1.820]	48.26 [1.900]	17	18	1-103634-7	
		43.69 [1.720]	45.72 [1.800]	16	17	1-103634-6	
	41.15 [1.620]	43.18 [1.700]	15	16	1-103634-5		
38.61 [1.520]	40.64 [1.600]	14	15	1-103634-4			
36.07 [1.420]	38.10 [1.500]	13	14	1-103634-3			
33.53 [1.320]	35.56 [1.400]	12	13	1-103634-2			
30.99 [1.220]	33.02 [1.300]	1 1	12	1-103634-1			
28.45 [1.120]	30.48 [1.200]	10	1 1	1-103634-0			
25.91 [1.020]	27.94 [1.100]	9	10	103634-9			
23.37 [.920]	25.40 [1.000]	8	9	103634-8			
20.83 [.820]	22.86 [.900]	7	8	103634-7			
18.29 [.720]	20.32 [.800]	6	7	103634-6			
15.75 [.620]	17.78 [.700]	5	6	103634-5			
13.21 [.520]	15.24 [.600]	4	5	103634-4			
10.67 [.420]	12.70 [.500]	3	4	103634-3			
8.13 [.320]	10.16 [.400]	2	3	103634-2			
5.59 [.220]	7.62 [.300]	1	2	103634-1			
	PLATING	C	B	A	NO. OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 3-5-91 S. SHUEY GW 3-27-91 L. CASTAGNA APVD 3-27-91 L. CASTAGNA		 TE Connectivity	
DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME HEADER ASSEMBLY, RIGHT ANGLE, SINGLE ROW, 2.54 [100] C/L 0.64 [025] 50 POST, WITH PLZN & LATCHING, AMPMODU MTE	
MATERIAL HOUSING		FINISH SEE TABLE		SIZE CAGE CODE DRAWING NO A1 00779 C=103634	
WEIGHT —		CUSTOMER DRAWING		RESTRICTED TO — SCALE 4:1 SHEET 1 OF 1 REV. U	