

## Housing - HC-B 24-SML-67/M1PG21 - 1771985


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting base, with single locking latch, height 67 mm, with screw connection, 1x Pg21



### Key commercial data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 10 pc  |
| GTIN                                 | <br>4 017918 036669 |
| Weight per Piece (excluding packing) | 414.1 g  |
| Custom tariff number                 | 85389099   |
| Country of origin                    | Germany  |

### Technical data

#### Dimensions

|                         |                 |
|-------------------------|-----------------|
| Height                  | 67 mm           |
| Width                   | 57 mm           |
| Length                  | 144 mm          |
| Wrench size, union nut  | 28 mm           |
| External cable diameter | 10 mm ... 19 mm |

#### Ambient conditions

|                                      |                   |
|--------------------------------------|-------------------|
| Degree of protection of housing (IP) | IP65              |
| Ambient temperature (operation)      | -40 °C ... 125 °C |

#### General

|                              |  |
|------------------------------|--|
| Type                         | B24  |
| Housing type                 | Box mounting bases                             |
| Locking type                 | With single locking latch                      |
| No. of cable outlets         | 1  |
| Cable exit                   | Left (view of the opened single locking latch) |
| Screw connection             | with   |
| Type of the screw connection | 1x Pg21  |

# Housing - HC-B 24-SML-67/M1PG21 - 1771985

## Technical data

### General

|                              |                             |
|------------------------------|-----------------------------|
| Housing material             | Aluminum die-cast           |
| Housing surface material     | Powder-coated, gray         |
| Seal material                | NBR                         |
| Cable gland material         | Nickel-plated brass         |
| Cable seal material          | NBR                         |
| Material lock                | Stainless steel, handle: PA |
| Material grip body interlock | PA                          |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000437 |
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

## Housing - HC-B 24-SML-67/M1PG21 - 1771985

### Approvals

---

Approvals submitted

---

### Approval details

|     |
|-----|
| EAC |
|-----|

### Drawings

Dimensioned drawing

