



## XCSB703

metal safety switch XCSB - 2 NC + 1 NO - slow break - 1 entry  
tapped 1/2" NPT



Download your XCSB703 datasheet



Characteristics | Documents & Downloads

### Main

Hide

Range of product	Preventa Safety detection
Product or component type	Safety switch
Component name	XCSB
Design	Industrial
Material	Metal
Head type	Key operated turret head
Contacts type and composition	2 NC + 1 NO
Contacts operation	Slow-break, break before make
Cable entry	1 entry tapped 1/2" NPT
Electrical connection	Terminal, 1 x 0.5...2 x 1.5 mm <sup>2</sup> with or without cable end
Number of poles	3
Locking options description	With locking of actuator, unlocking by pushbutton
Local signalling	Without

### Complementary

Hide


Positive opening	With NC contact
Mechanical durability	600000 cycles
Minimum actuation speed	0.01 m/s
Maximum actuation speed	0.5 m/s
[Ie] rated operational current	6 A at 120 V utilisation category AC-15, A300 conforming to EN/IEC 60947-5-1 3 A at 240 V utilisation category AC-15, A300 conforming to EN/IEC 60947-5-1 0.55 A at 125 V utilisation category DC-13, Q300 conforming to EN/IEC 60947-5-1 0.27 A at 250 V utilisation category DC-13, Q300 conforming to EN/IEC 60947-5-1
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	500 V conforming to EN/IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-5-1
Short circuit protection	10 A cartridge fuse type gG (gl)
Actutr forcible withdrawal rtc	1500 N
Actuator force for extraction	>= 20 N
Operating rate	10 cyc/mn for maximum durability
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to EN/IEC 61508

<b>Safety reliability data</b>	B10d = 5000000 (value given for a life time of 20 years limited by mechanical or contact wear)
<b>Body material</b>	Zamak
<b>Head material</b>	Zamak
<b>Depth</b>	44 mm
<b>Height</b>	114 mm
<b>Width</b>	52 mm
<b>Product weight</b>	0.475 kg

## Environment - Hide

<b>Standards</b>	EN 1088/ISO 14119 EN/IEC 60204-1 EN/IEC 60947-5-1 EN/ISO 12100 UL 508 CSA C22.2 No 14
<b>Product certifications</b>	CSA UL
<b>Protective treatment</b>	TC
<b>Ambient air temperature for operation</b>	-25...70 °C
<b>Ambient air temperature for storage</b>	-40...70 °C
<b>Vibration resistance</b>	5 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
<b>Shock resistance</b>	10 gn for 11 ms conforming to IEC 60068-2-27
<b>Class of protection against electric shock</b>	Class I conforming to EN/IEC 60536
<b>IP degree of protection</b>	IP67 conforming to EN/IEC 60529 and EN/IEC 60947-5-1

## Offer Sustainability - Hide

<b>Sustainable offer status</b>	Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 1103 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available  <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Need no specific recycling operations

## Contractual warranty - Hide

<b>Period</b>	18 months
---------------	-----------