


UWS

Unvented water storage heaters



- Effective and fast mains fed unvented water storage heater
- Small and compact enables undersink installation where space is limited
- Unique ohmic resistance for reinforced protection against corrosion
- High efficiency water inlet



Key Features

- High quality enamel lined tank
- Large magnesium anode
- CFC-free high density insulation foam
- Expansion relief valve
- Externally adjustable rod type thermostat with integrated security
- Indicator light when operating
- 1 year UK guarantee

Technical Specification

- kW loading at 240V: 2.2kW
- kW loading at 230V: 2kW
- Weight when full 10L: 17.5kg
- Weight when full 15L: 25kg
- Operating pressure: 1.5 bar - 6 bar
- 2 dielectric union
- Sheathed copper immersion element
- Electrical connection 230-240V AC 3kW (13 Amps) is required

Product Range

Product Ref.	Finish	Model	Cat No.
UWS 10 Litre	White	UWS10	47784570
UWS 15 Litre	White	UWS15	47784571
Optional Cold Water Pack		CWP	87783101
Tundish		TUN	97783238
Temperature/Pressure Relief Valve		TPR	97783258
Thermostatic Blending Valve		TBV	87783103

262mm



456mm

ø 255mm



Dimensions 10L

294mm



493mm

ø 287mm



Dimensions 15L