

**Product-type designation**

**SCALANCE W786-2RR**



IWLAN ACCESS POINT SCALANCE W786-2RR,  
 ONLY FOR USE IN USA,  
 IEEE 802.11B/G/A/H,  
 INDUSTRIAL WIRELESS LAN WITH RAPID ROAMING  
 (IWLAN RR),  
 2.4/5 GHZ, UP TO 54MBIT/S,  
 WPA2/802.11I/11E,  
 NOTE NATIONAL APPROVALS, ONLY F. USA,  
 48VDC,IP65(-40-+70 GRD C),  
 4XINTERNAL ANTENNAS,  
 2 RADIO INTERFACES, POE,  
 RJ45 (TWISTED PAIR) SOCKET SCOPE OF SUPPLY.:  
 MOUNT. MAT.,  
 DOCU ON CD IN GERMAN AND ENGLISH;

**Transmission rate**

Transfer rate

- with W-LAN / maximum
- with Industrial Ethernet
- note

54 Mbit/s

10 ... 100 Mbit/s

Due to the simultaneous use of several radio channels, a transmission rate of 108 Mbit/s is possible (turbo mode)

**Interfaces**

Number of electrical connections

- for network components and terminal equipment
- for power supply
- for redundant power supply

1

1

1

Design of electrical connection

- for network components and terminal equipment
- for power supply

RJ45 socket

2-pole connector (48 V DC) or optionally available power supply adapter (4-pole 12 to 24 V DC or 3-pole 100 to 240 V AC)

design of the removable storage / C-PLUG

Yes

**Interfaces / wireless**

Number of radio cards / permanently installed

2

Number of internal antennas

4

**Supply voltage, current consumption, power loss**

Type of voltage / of supply voltage	DC
Supply voltage	
• 1 / from terminal block	48 V
• from Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	48 V
• from optional integratable power supply	
• with AC	100 ... 240 V
• with DC	12 ... 24 V
Current consumed	
• at 24 V / with DC / typical	0.34 A
• at 48 V / with DC / typical	0.17 A
• at 230 V / with AC / typical	0.04 A
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.34 A
Active power loss	
• at 24V / for DC / typical	8 W
• at 48 V / with DC / typical	8 W
• at 230 V / with AC / typical	8 W
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	8 W
<b>Permitted ambient conditions</b>	
Ambient temperature	
• during operating	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Relative humidity / at 25 °C / without condensation / during operating / maximum	100 %
Protection class IP	IP65
Ambient condition / for (standard) operation mode	When using the power supply 100 to 240 V AC, an operating temperature of -40 °C to +60 °C is permissible
<b>Design, dimensions and weight</b>	
Width / of enclosure / without antenna	251 mm
Height / of enclosure / without antenna	251 mm
Depth / of enclosure / without antenna	72 mm
Net weight	2.24 kg
Type of mounting	
• wall mounting	Yes
Type of mounting	For mast mounting, 35 mm DIN rail mounting and S7-300 rail mounting, an additional support plate is required
<b>Wireless frequencies</b>	
Radio frequency	
• for WLAN in 2.4 GHz frequency band	2.41 ... 2.48 GHz

- for WLAN in 5 GHz frequency band

4.9 ... 5.8 GHz

### Product properties, functions, components / general

Number of SSIDs	16
Product function	
• Dual Client	Yes
• iHOP	Yes
• iPCF	Yes
• iPCF-MC	Yes
Number of iPCF-capable radio modules	1

### Product functions / management, configuration

Number of manageable IP addresses / in client	8
Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• configuration with STEP 7 in the TIA Portal	Yes
• SMTP server	Yes
• operation with IWLAN controller	No
• operation with Enterasys WLAN controller	No
• iQoS	Yes
• forced roaming with IWLAN	Yes
• WDS	Yes
Protocol / is supported	
• Address Resolution Protocol (ARP)	Yes
• ICMP	Yes
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• DCP	Yes
• LLDP	Yes
Identification & maintenance	
• I&M0 - device-specific information	Yes
• I&M1 - plant identification/location name	Yes

Product functions / Diagnosis	
Product function	
• PROFINET IO diagnosis	Yes
• Link Check	Yes
• connection monitoring IP-Alive	Yes
• localization via Aeroscout	Yes
• SysLog	Yes
Product functions / VLAN	
Product function / function VLAN with IWLAN	Yes
Product functions / DHCP	
Product function / DHCP client	Yes
Product functions / Redundancy	
Protocol / is supported / STP/RSTP	Yes
Product functions / Security	
Product function	
• ACL - MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
Protocol / is supported / SSH	Yes
Product functions / Time	
Protocol / is supported / SNTP	Yes
Standards, specifications, approvals	
Standard	
• for EMC / from FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for safety / of CSA and UL	UL 60950-1 CSA C22.2 No. 60950-1
• for hazardous area / of CSA and UL	UL 1604, CSA C22.2 No. 213-M1987, CL. 1, Div. 2, GP. A,B,C,D, T4 / CL. 1, Zone 2, GP IIC, T4
Verification of suitability	
• CE mark	Yes
• EC declaration of conformity	Yes
• C-Tick	Yes
• CCC	No
• Railway application in accordance with EN 50155	No
• e1 approval	Yes

• E1 approval	Yes
• NEMA4X	Yes
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	Yes
Standard for wireless communication	
• IEEE 802.11a	Yes
• IEEE 802.11b	Yes
• IEEE 802.11e	Yes
• IEEE 802.11g	Yes
• IEEE 802.11h	Yes
• IEEE 802.11i	Yes
• IEEE 802.11n	No
Wireless approval	For operation in the USA, you can find more detailed information at: <a href="http://www.siemens.com/simatic-net/ik-info">www.siemens.com/simatic-net/ik-info</a>
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	No
<b>Accessories</b>	
Accessories	48 V DC screw terminal included in scope of delivery
<b>letzte Änderung:</b>	Feb 27, 2012