






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE APPROVED
✓			0	RELEASE DRAWING PER M-6939	5-11-82 MSF/DH
✓			A	Added 643030-4, TTI B2-164	1/20/83 DH/DH
✓			A1	RESTORED	7/11/85 BD RS
✓			B	REV PER ECN CM 705	12/1/86 TB / RS
✓			C	REV PER EC 0730-0201-94	4-26-85 JH RS



ASSEMBLY DETAILS

- 1 SHEET METALS SCREWS NOT SUPPLIED.
2 TWO REQUIRED PER CONNECTOR.
3. STYLE A; MAX WIRE BUNDLE WITHOUT INSERT IS 5 AT .190 DIA, AND MIN WIRE BUNDLE WITH INSERT IS 5 AT .040 DIA.
4. STYLE B; DESIGNED TO ACCEPT CABLE WITH .200-.350 OUTSIDE DIAMETER.
6. DETACHABLE INSERT MAY SEPARATE FROM STRAIN RELIEF BODY DURING SHIPPING.

NO INSERT	BRICK RED OR WHITE	NYLON 94V-0	STYLE B	643030-4/2
WITH INSERT	NATURAL	NYLON 94V-2	STYLE A	643030-3/2
NO INSERT			STYLE B	643030-2/2
WITH INSERT	BRICK RED OR WHITE	NYLON 94V-0	STYLE A	643030-1/2
	5	COLOR	MATERIAL	TYPE
				PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±	CONTRACT NO DR <i>m. Feker</i> 5-11-82 CHK <i>D.S. Heide</i> 6/1/82 APPD <i>G.E. Acella</i> 6/1/82 APPD DSGN APPD OTHER APPD	AMP INCORPORATED Harrisburg, Pa. 17105 NAME STRAIN RELIEF AND INSERT, UNIVERSAL MATE-N-LOK™, 5 CIRCUIT SIZE C FSCM NO 00779 DRAWING NO 643030 SCALE 2-1 SHEET 1 OF 1
MATERIAL SEE TABLE		