


IZ5047

IZB31.5-BPKG/2M PVC

Inductive sensors


Product characteristics

Inductive sensor

Metal housing Ø 4 mm

Cable

Sensing range 1.5 mm; [nf] non-flush mountable

Electrical data

Electrical design	DC PNP
Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10 (24 V)
Reverse polarity protection	yes

Outputs

Output function	normally open
Voltage drop [V]	< 3
Current rating [mA]	100
Short-circuit protection	pulsed
Overload protection	yes
Switching frequency [Hz]	1800

Range

Sensing range [mm]	1.5
Real sensing range (Sr) [mm]	1.5 ± 10 %
Operating distance [mm]	0...1.2

Accuracy / deviations

Correction factors	mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis [% of Sr]	< 15
Switch-point drift [% of Sr]	-10...10

Environment

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2 EN 55011: class B
MTTF [Years]	835

Mechanical data


Mounting	non-flush mountable
Housing materials	housing: stainless steel; active face: POM (polyoxymethylene)

IZ5047

IZB31.5-BPKG/2M PVC

Inductive sensors

Installation



If S_r varies by $< 10\%$
the following free space must be maintained:
 $X > 1.5\text{ mm}$ for ferromagnetic materials
 $X > 3.0\text{ mm}$ for other metals

Weight	[kg]	0.059
--------	------	-------

Displays / operating elements

Output status indication	LED	red (4 x 90°)
--------------------------	-----	---------------


Electrical connection

Connection	PVC cable / 2 m; 3 x 0.14 mm ²
------------	---

Wiring

Core colours

BK black
BN brown
BU blue



Accessories

Accessories (included)	Mounting clamp
------------------------	----------------

Remarks

Pack quantity	[piece]	1
---------------	---------	---