


remote trip isolating switches DX™ - IS

from 16 A to 125 A




Dimensions (p. 183)
Technical characteristics (p. 156-158)

AC 22 A according to IEC 60947 - 3
Double break contacts

Pack	Cat.Nos	Remote trip head isolating switches	
		Red handle (main device) Visible contact indication Remote tripping with associated control auxiliary Compatible with the following auxiliaries: - Control auxil. Cat.No 073 60/61/65/66/68/69 (p. 154) - Signalling auxil. Cat.No 073 50/54 (p. 154) Visual indication of the actual status of the contacts: - Closed position or fault (red indicator - I) - Open position (green indicator) on handle In case of fault when opening, the red position indicator indicates the faulty pole and the handle is in the central position	
		2P - 400 V~	
		Nominal rating (A)	Number of modules
2	023 56	40	2
2	023 57	63	2
2	023 58	100	2
2	023 59	125	2
		3P - 400 V~	
1	023 66	40	3
1	023 67	63	3
1	023 68	100	3
1	023 69	125	3
		4P - 400 V~	
1	023 76	40	4
1	023 77	63	4
1	023 78	100	4
1	023 79	125	4

isolating switches DX™ - IS

from 16 A to 125 A



Dimensions (p. 183)
Technical characteristics (p. 156-158)

AC 22 A according to IEC 60947 - 3
Double break contacts

Pack	Cat.Nos	Isolating switches	
		Can be equipped with 1 signalling auxiliary Cat.Nos 073 50 or 073 54 (p. 154) 1P - 250 V~ Nominal rating (A)	
			Number of modules
10	043 01	16	1
10	043 02	20	1
10	043 05	32	1
10	043 07	40	1
10	043 10	63	1
10	043 14	100	1
		1P with indicator - 250 V~ Supplied with lamp	
10	043 03	20	1
		2P - 400 V~	
10	043 21	16	1
10	043 22	20	1
10	043 25	32	1
5	043 27	40	2
5	043 30	63	2
5	043 34	100	2
5	043 38	125	2
		2P with indicator - 250 V~ Supplied with lamp	
10	043 23	20	1
10	043 26	32	1
		3P - 400 V~	
5	043 42	20	2
5	043 45	32	2
3	043 47	40	3
3	043 50	63	3
3	043 54	100	3
3	043 58	125	3
		4P - 400 V~	
5	043 62	20	2
5	043 65	32	2
2	043 67	40	4
2	043 70	63	4
2	043 74	100	4
2	043 78	125	4



For three-phase version, please consult us