

MB5A10C2

Article Number: 151-28529

Adhesive Bases, .35" Max tie width, .19" Hole Dia., 1.49" Length/Width, PA66, White, 100/pkg



Download spec sheet

Base Data

Local Order Number	MB5A10C2
Type	MB5A
Color	White (WH)
Features and Benefits	<ul style="list-style-type: none"> • For use with 18 and 30 pound cable ties to provide stability when securing bundles. • Secures with rubber based adhesive backing and/or two or four screws. • 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
Product Description	HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.
Fixation Method (FF)	Screw Mounting and Adhesive
Short Description	Adhesive Bases, .35" Max tie width, .19" Hole Dia., 1.49" Length/Width, PA66, White, 100/pkg

Product Dimensions

Length L (imperial)	1.49 "
Length L (metric)	37.7 mm
Width W (imperial)	1.49 "
Width W (metric)	37.7 mm
Cable Tie Width Max (imperial)	0.35 "
Cable Tie Width max. (metric)	8.9 mm
Height H (imperial)	0.28 "
Height H (metric)	7.1 mm
Mounting Hole Diameter D (imperial)	0.19 "
Mounting Hole Diameter D (metric)	4.8 mm
Mounting Hole Centers (imperial)	1.0 "
Thickness of Adhesive TA (imperial)	0.031 "
Mounting Hole Centers (metric)	25.3 mm
Thickness of Adhesive TA (metric)	0.8 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	100
Carton Quantity	1000 Pieces
Weight (Metric)	1.8 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Shortcut Adhesive	Synthetic rubber
Adhesive Operating Temperature	-4°F to +122°F (-20°C to +50°C)
CSA Certified	No
Flammability	UL94 V2 (excluding adhesive)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Conformity	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes