

Electronic housing - ME MAX 17,5 SF G 2-2 KMGY - 2901369

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Component housing without vents, Complete housing, Cross connection: DIN rail bus connector, Color: light gray, Width: 17.5 mm, Constructional height: 70.4 mm, Number of positions cross connector: 5

Why buy this product

- Labels for additional labeling as an option
- DIN rail bus connector as an option
- Plug-in connection with screw, spring-cage or fast connection technology
- Large PCB surface despite compact housing dimensions
- Large front surface for high-pos. plugs or operating and setting elements
- The fitted cover is easy to adapt and print
- Easy module replacement without interrupting the contact chain
- Transparent front cover can be swiveled
- Functional earth ground contact as an option
- Fixed or plug-in connection technology can be combined on up to three connection levels, with different pitches



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 178525
Weight per Piece (excluding packing)	26.6 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color	light gray

Ambient conditions

Electronic housing - ME MAX 17,5 SF G 2-2 KMGY - 2901369

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C (depending on power dissipation)
---------------------------------	---

Dimensions

Length	85 mm
Constructional height	70.4 mm
Width	17.5 mm

Technical data

Inflammability class according to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	3.2 W 5.9 W

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Electronic housing - ME MAX 17,5 SF G 2-2 KMGY - 2901369

Approvals

Ex Approvals

Approvals submitted

Approval details


UL Recognized

cUL Recognized

cULus Recognized

Drawings

Dimensioned drawing



A = 70.4 mm; B = 17.5 mm; C = 85 mm