

Keyhole Clips



SR 1970

Natural Nylon 6.6

- Easy finger-pressure assembly
- Good electrical insulation
- Vibration, abrasion and corrosion resistant



Part Number	Dimensions (mm)			Std Pack Qty
	Hole Diameter (mm)	Maximum Panel Thickness	D	
460402	3.18	2.36	6.35	1000
460403	3.18	3.18	6.35	1000
460404	3.18	3.96	6.35	1000
460405	3.18	4.78	6.35	1000
460406	3.18	5.56	6.35	1000
460407	3.18	6.35	6.35	1000
460408	3.96	2.36	7.94	1000
460409	3.96	3.18	7.94	1000
460410	3.96	3.96	7.94	1000
460411	3.96	4.75	7.94	1000
460412	3.96	5.54	7.94	1000
460413	3.96	6.35	7.94	1000
460414	3.96	7.14	7.94	1000
460416	3.96	8.71	7.94	1000
460417	3.96	9.53	7.94	1000
460418	5.56	2.36	8.73	1000
460419	5.56	3.18	8.73	1000
460420	5.56	3.96	8.73	1000
460421	5.56	4.78	8.73	1000
460422	5.56	5.56	8.73	1000
460423	5.56	6.35	8.73	1000
460424	5.56	7.14	8.73	1000
460425	5.56	7.92	8.73	1000
460426	6.35	2.36	12.70	1000
460427	6.35	3.18	12.70	1000
460428	6.35	3.96	12.70	1000
460429	6.35	4.75	12.70	1000
460430	6.35	5.56	12.70	1000
460431	6.35	6.35	12.70	1000
460432	6.35	7.14	12.70	1000
460433	6.35	7.92	12.70	1000
460434	6.35	8.71	12.70	1000
460435	6.35	9.53	12.70	1000




Drive Fastener

DF/DFVO

Color: Natural



Material: UL94 HB Acetal, RMS-14A	Material: UL94 V0 Nylon 6/6, RMS-19	Hole Ø	Total Holding Thickness	"D"	"H"	"L" Ref.	"W" Ref.	Std Pack Qty
DF-137-010	DFVO-137-010	3.2	1 - 4.5	8	1.5	13	2.7	1000
DF-137-020	DFVO-137-020	3.9	1 - 5	9	1.6	14	2.9	1000
DF-137-030	DFVO-137-030	4.7	1 - 5.5	10	1.7	15	3.4	1000
DF-137-031	DFVO-137-031	4.7	1 - 5.5	11	2.9	15	3.4	1000
DF-137-040	DFVO-137-040	6.4	1.5 - 6.5	12	2	17	3.9	1000
DF-137-050	DFVO-137-050	7.8	1.5 - 7	14	2.2	19	4.2	1000
DF-137-060	DFVO-137-060	5.5	6 - 9	12	2	17.5	3.8	1000



Arrow Clips

SR 1969

Natural Nylon 6.6 or POM

- Good electrical insulation
- Vibration, abrasion and corrosion resistant



Part Number	Panel Hole Dia (mm)	Dimensions (mm)					Std Pack Qty
		Panel Thickness (mm)	D	h1	H	d	
460387	2.16-2.29	0.81-2.72	3.18	0.76	4.75	2.72	1000
460388	3.00-3.10	1.57-3.18	7.11	1.52	9.91	3.71	1000
460389	3.02-3.43	1.58-3.18	6.86	1.01	8.38	3.56	1000
*137000800005	3.5	1.0-4.5	8.0	1.5	13.0	3.2	500
460390	3.84-4.09	1.57-3.18	7.11	1.02	9.91	4.98	1000
460391	3.84-4.09	1.57-3.68	7.11	2.03	10.16	4.57	1000
*137002000005	4.0	1.0-5.0	9.0	1.6	14.0	3.9	500
460392	4.06-4.19	0.81-3.18	7.11	2.03	10.16	4.72	1000
460393	4.62-4.88	1.57-3.18	9.14	1.52	10.16	5.72	1000
460394	4.62-4.88	4.19-4.70	9.53	1.52	13.33	5.23	1000
*137003000005	5.0	1.0-5.5	10.0	1.7	15.0	4.7	500
*137006000005	6.0	6.0-9.0	12.0	2.0	18.0	5.5	500
460400	8.38-8.64	3.18-8.88	17.45	0.75	22.74	9.4	1000
460401	8.51-8.76	1.57-3.56	22.0	1.27	11.43	9.22	1000

* Made from POM

