




AVB 3,2/2/24*

Short circuit proof PCB transformer

- Maximum power from minimum size
- Vacuum resin moulded (self extinguishing to UL 94 V-0)

Short circuit proof safety isolating transformer to IEC 61558-2-6, DIN EN 61558-2-6, VDE 0570 part 2-6

*Transformer to IEC 61558-2-1, DIN EN 61558-2-1, VDE 0570 part 2-1 (without VDE-Approval)



AVB 3,2/2/24*

Short circuit proof PCB transformer



Input data	
Input voltage	2x115 V
Frequency range	50 - 60 Hz
No-load loss (typ.)	0.5 W
Output data	
Output voltage	2x24 V
No-load voltage (ca. x factor)	1.57
Efficiency	58 %
Power	3.20 VA
Standards and security	
Approvals	C-UL-US, ENEC 10 (VDE)
Protection index	IP 00
Safety class (prepared)	I
Ambient temperature max.	50 °C
Class of Insulation System	VDE=E, UL=105
Test voltage	5000 V, 50 Hz
Mechanical data	
Type	encapsulated
Core type	EI 38/16,5
Terminals	Pins for printed circuit boards
Pin (∅)	0,6 x 0,8
Wide	35 mm
Height	30.8 mm
Depth	41 mm
Weight	0.17 kg
Order numbers	
Order Number	AVB 3,2/2/24*

BLOCK Transformatoren-Elektronik GmbH
 Max-Planck-Straße 36-46
 27283 Verden
 Germany
 Phone +49 4231 678-0
 Fax +49 4231 678-177