

Classic ECO A55

Classic ECO A55 53W E27 240V Sleeve

0023134



Range features

- 1:1 replacement of Incandescent A55 lamp
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable
- Average rated life 1500hrs or 2000hrs - up to two times more average life compared to incandescent lamps



PRODUCT OVERVIEW

Ordering number	0023134
Light colour	828 Homelight
Technology	Halogen
Energy class	D
Average life (Rated) (h)	2000
Lamp finish	Clear
Lamp shape	GLS A55
Dimmable	Yes
Cap/Base	E27
Type	Classic 'A' Shape
EAN code	5410288231341
CRI (Ra)	100
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	845
Watt (Nominal) (W)	53
Equivalent watt (W)	70
Voltage (V)	240

Classic ECO A55

Classic ECO A55 53W E27 240V Sleeve

0023134

DATA TABLE

General data

Ordering number	0023134
Technology	Halogen
Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp shape	GLS A55
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E27
Type	Classic 'A' Shape
EAN code	5410288231341
E-number SE	8355979
E-number FI	4740147
Long description	1:1 replacement of Incandescent A55 lamp. More efficient - more savings. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable. Average rated life 1500hrs or 2000hrs - up to two times more average life compared to incandescent lamps
Product name	Classic ECO A55 53W E27 240V Sleeve
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Classic ECO A55

Classic ECO A55 53W E27 240V Sleeve

0023134

Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	845
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	845

Electrical data

kWh per 1000 hours burning time	53
Watt (Rated) (W)	53
Watt (Nominal) (W)	53
Equivalent watt (W)	70
Voltage (V)	240
Lamp power factor	1

Physical data

Lamp Length (mm) - C/L	100
Lamp Diameter (mm) - D	56
Packaging outer width (cm)	30
Packaging outer length (cm)	59.5
Packaging outer height (cm)	22
Packaging single width (cm)	5.5
Packaging single length (cm)	5.5
Packaging single height (cm)	9.6


Classic ECO A55

Classic ECO A55 53W E27 240V Sleeve


0023134

TECHNICAL DRAWINGS

Classic ECO A55



E27



ENERGY LABEL

