

J1: 0.8mm 26Pin Male

J2: DB-25 Male


LABLE DETAIL


CAB-SS-232MT

| ITEM | DESCRIPTION                                                                                                                                        | Q'TY | UNIT |
|------|----------------------------------------------------------------------------------------------------------------------------------------------------|------|------|
| 1    | 0.8mm 26PIN CONNECTOR; MALE                                                                                                                        | 1    | PCS  |
| 2    | CISCO BLUE MOLDED PVC HOOD                                                                                                                         | 1    | PCS  |
| 3    | METAL CAN: PRE-MOLD THE PE COVER ONTO THE CONNECTORS.<br>360° COPPER FOIL SOLDERING.                                                               | 1    | PCS  |
| 4    | 4/40 ALL METAL THUMBSCREW                                                                                                                          | 2    | PCS  |
| 5    | (28AWG UL2919) X 9 TMST PAIR; 100%AL FOIL SHIELD +<br>90% MIN. BRAID SHIELD OVERALL; CISCO BLUE PVC OUTER<br>JACKET SEE WIRE SPEC FOR MORE DETAILS | 10   | FEET |
| 6    | CISCO BLUE MOLDED 4/40 THUMBSCREW                                                                                                                  | 2    | PCS  |
| 7    | METAL CAN:                                                                                                                                         | 1    | PCS  |
| 8    | CISCO BLUE MOLDED PVC HOOD                                                                                                                         | 1    | PCS  |
| 9    | DB25 CONNECTOR: MALE                                                                                                                               | 1    | PCS  |
| 10   | CABLE LABLE: PLEASE SEE DETAIL                                                                                                                     | 1    | PCS  |

| Electrical Test :                         |
|-------------------------------------------|
| 1. Contact Resistance : Max. 2.0 ohms     |
| 2. Insulation Resistance : Min. 5.0 Mohms |
| 3. Hi-pot : 300V DC / 10ms                |

PIN ASSIGNMENT:



|          |      |         |         |        |            |           |              |                                                                                                            |         |
|----------|------|---------|---------|--------|------------|-----------|--------------|------------------------------------------------------------------------------------------------------------|---------|
| △        |      |         |         | Data   | 1999,09,26 | Model No. | CAB-SS-232MT |  <b>RS Components</b> |         |
| △        |      |         |         | Design |            | Part Name | CAB-SS-232MT |                                                                                                            |         |
| △        |      |         |         | Check  |            | DWG.No.   | CAB-SS-232MT |                                                                                                            | Version |
| Revision | Data | Content | Confirm | Design | Confirm    |           |              |                                                                                                            |         |