

EAN CODE : 3760244880260



12V + ACTIVE PFC

ALE1210

- PRECISE** : Output ripple < 3mV rms.
- COMPLIE** : EN 61000-3-2 Built in active power corrector (PFC).
- PRACTICAL** : Output voltage adjustable from 10 to 15V.
- PROTECTED** : Short circuit protection.
- EASY** : Direct DIN rail mounting.
- Dual spring terminal block.



120 WATTS
12V (Adj. 10 to 15V)
10A



Specifications

Voltage

- Floating outputs on dual spring terminal block for 2.5mm² (AWG 12) wire
- Output voltage : adjustable from 10 to 15V.
- Regulation : < 25mV for a load variation from 0 to 100%.
< 1mV for a line variation from 190 to 253V.
- Ripple : < 3mV rms including:
< 5mV peak to peak of the signal at 100 KHz
< 5mV peak to peak of the signal at 100 Hz
< 35mV peak to peak of switching spikes
- Hold-up time : 25 ms at half load and 12 ms at full load (190V line input).
- Indicator : green power-on LED indicator.
"status, output fault" red LED.

Current

- Max I : 10,5A in short circuit condition.
10A from 10 to 15V

Power

- Max output power : 150W.

Protection

- Short circuit protection, by current limit.
- Against overcurrent on main input, by fuse.
- Output overload protection by voltage limiting to 17V.

Other specifications

- Safety : Classe I, complies with EN 60950.
- EMC : Complies with EN 61000-6-2 and EN 61000-6-4.
- Protection level : IP 30.
- Input voltage : 190 to 253 Volts, 50 / 60 Hz.
- Mains input : Dual spring terminal block for 2.5mm² (AWG 12) wire.
- Power consumption : 170 W max.
- Power factor : 0,99 (built in PFC).
- Dielectric strength : 4000V.
1500V from input to chassis.
- Presentation : galvanized steel case and front panel with epoxy finish.
- Mounting : Integral symmetrical DIN rail clips.