


VB 1,5/1/9

Short circuit proof PCB transformer


- Maximum power from minimum size
- Vacuum resin moulded (self extinguishing to UL 94 V-0)

Short circuit proof safety isolating transformer to IEC 61558-2-6, DIN EN 61558-2-6, VDE 0570 part 2-6

*Transformer to IEC 61558-2-1, DIN EN 61558-2-1, VDE 0570 part 2-1 (without VDE-Approval)



Dimensions in mm



VB 1,5/1/9

Short circuit proof PCB transformer



Input data	
Input voltage	230 V
Frequency range	50 - 60 Hz
No-load loss (typ.)	1.0 W
Output data	
Output voltage	9 V
No-load voltage (ca. x factor)	1.39
Efficiency	57 %
Power	1.50 VA
Standards and security	
Approvals	C-UL-US, ENEC 10 (VDE)
Short circuit strength	inherently short-circuit proof
Protection index	IP 00
Safety class (prepared)	II
Ambient temperature max.	70 °C
Class of Insulation System	VDE=B, UL=105
Test voltage	5000 V, 50 Hz
Mechanical data	
Type	encapsulated
Core type	EI 30/12,5
Terminals	Pins for printed circuit boards
Pin (∅)	0.8 mm
Weight	0.08 kg
Order numbers	
Order Number	VB 1,5/1/9

BLOCK Transformatoren-Elektronik GmbH

Max-Planck-Straße 36-46

27283 Verden

Germany

Phone +49 4231 678-0

Fax +49 4231 678-177