







VIEW H



SECT. J-J
SCALE 20:1

D) I) D)	0.28 ±0.03	13.65	17	12.5	18.2	54548-2670	54548-26 19	26
	0.3 ±0.03	12.65	16	11.5	17.2	54548-2470	54548-24 19	24
		11.65	15	10.5	16.2	54548-2270	54548-22 19	22
		11.15	14.5	10	15.7	54548-2170	54548-21 19	21
		10.65	14	9.5	15.2	54548-2070	54548-20 19	20
		10.15	13.5	9	14.7	54548-1970	54548-19 19	19
		9.65	13	8.5	14.2	54548-1870	54548-18 19	18
		9.15	12.5	8	13.7	54548-1770	54548-17 19	17
		8.65	12	7.5	13.2	54548-1670	54548-16 19	16
		8.15	11.5	7	12.7	54548-1570	54548-15 19	15
		7.65	11	6.5	12.2	54548-1470	54548-14 19	14
		7.15	10.5	6	11.7	54548-1370	54548-13 19	13
		6.65	10	5.5	11.2	54548-1270	54548-12 19	12
		6.15	9.5	5	10.7	54548-1170	54548-11 19	11
		5.65	9	4.5	10.2	54548-1070	54548-10 19	10
		5.15	8.5	4	9.7	54548-0970	54548-09 19	9
		4.65	8	3.5	9.2	54548-0870	54548-08 19	8
		4.15	7.5	3	8.7	54548-0770	54548-07 19	7
		3.65	7	2.5	8.2	54548-0670	54548-06 19	6
		3.15	6.5	2	7.7	54548-0570	54548-05 19	5
2.65	6.0	1.5	7.2	54548-0470	54548-04 19	4		
THICKNESS OF FPC	D	C	B	A	EMBOSSD TAPE ORDER No. オーダー番号	製品番号 MATERIAL No.	極数 CIRCUIT	

REVISED	EC NO: J2008-4048	DRWN:MNABEI CH'KD:THARYAMA APPR:NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				10 UNDER	± 0.2	DRAWN BY Y. WADA	DATE 2004/01/09	TITLE 0.5 FPC CONN ZIF HSG ASSY FOR SMT RA BTM CONT -LEAD FREE-				
				10 OVER 30 UNDER	± 0.25	CHECKED BY M. SASAO	DATE 2004/01/09					
				30 OVER	± 0.3	APPROVED BY M. SASAO	DATE 2004/01/09	MOLEX MOLEX INCORPORATED				
				ANGULAR ±3 °	MATERIAL NO.		DOCUMENT NO.					
REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE		SD-54548-037		1 OF 2				
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												

10

9

8

7

6

5

4

3

2

1

F




E

D


C

B


A

DETAIL FNOTES

- 製品詳細寸法については図面 SD-54548-037 を参照下さい。
RE DETAILED DIMENSION, SEE SD-54548-037.
- 梱包数量：3000個/リール
NUMBER OF CONNECTORS : 3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- トップテープの剥離強度：0.1N ～ 1.3N { 10gf ～ 130gf }
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE : 0.1N ～ 1.3N(10gf ～ 130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED , DURING TRANSPORTATION.



- 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOPTAPE)：PET , PE , PEF
リール(REEL)：ポリスチレン (P.S) <リサイクル材を含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>
- 本製品は54548-**-90の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54548-**-90.

F

E

D

C

B

A

9

8

7


6

5

4

3

2



SECT. X-X

		54548--*70		MODEL NO.	
ANCES ED)	DIMENSION STYLE MM ONLY	SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	

tb_frame_A3_J_ME_S
Rev. D 2004/04/02

