


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			J1	REVISED PER ECO-11-005294	05APR11
					HMR



- 1 ALTERNATE PVC INSULATION MATERIAL FOR FOREIGN SUBSIDIARIES ONLY.
- 2 THIS IS NOT A U.S. MILITARY QUALIFIED PART
- 3 DIMENSION APPLIES FROM EDGE OF METAL WIRE BBL TO CENTER OF STUD HOLE.

WIRE INSULATION DIA. = .150 - .250
TONGUE MATERIAL THK. = .040 ±.002
TIN PLATE (MIL-T-10727)

OBSOLETE

2	2500	ON TAPE, REEL	3-35108-2
2	500	LOOSE PIECE	3-35108-1
2	100	LOOSE PC, BOX	8-35108-1
2	500	ON TAPE, LG. BOX	2-35108-3
MS25036-156 CLASS 2	2500	ON TAPE, REEL	2-35108-1
MS25036-156 CLASS 1 & 2	500	LOOSE PIECE	35108
MILITARY PART NO. & CLASS	QTY.	DESCRIPTION	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.008 ANGLES ±5°	CONTRACT NO		 TE Connectivity		
	DR UTA/RFB 9-24-85				
	MATERIAL INSULATION:  NYLON-YELLOW BODY & SLEEVE: COPPER (QQ-C-576)	CHK <i>P. Muthy 12.16.85</i>	NAME		WIRE TERMINAL P.I.D.G. RING TONGUE WIRE SIZE: 12-10
		APPD <i>GA 12.16.81</i>	SIZE		
FINISH BODY: SEE NOTE	DSGN APPD	FSCM NO		DRAWING NO	
	OTHER APPD	B 00779		35108	
		SCALE NTS		SHEET 1 OF 1	