







Angled terminal blocks spring clamp

Standard

 DIN 3



End stop		th. 9 mm	BADL	V0	1SNA 399 903 R0200
End stop		th. 10 mm	BAM2 V0	V0	1SNA 399 967 R0100
Rail		35 x 7,5 x 1	PR3.Z2		1SNA 174 300 R1700
Rail		35 x 15 x 2,3	PR4		1SNA 168 500 R1200
Rail		35 x 15 x 1,5	PR5		1SNA 168 700 R2200

Other end stops, rails and accessories : see section on accessories.


Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.



Terminal block body material is UL 94 V0.

* ABB Entelec spring connection terminal blocks comply with IEC 947-1 standard for 2.5 mm² rated wire size. Never the less, our spring terminal blocks can be connected to 4 mm² rigid wires.

Accessories



- 1 End section grey
- 2 Test plug black
- 3 Jumper bar orange
IP 20 - 24 A




- 4 Shield connector













R See section on marking method

D 2,5/5.I.3L

Spacing 5 mm +0,05 (.198")



3 springs + 1 test + 2 interconnections.

					
Color	Type	Part number			
Grey	 D 2,5/5.I.3L	1SNA 399 068	R1700		
Blue	 D 2,5/5.I.N.3L	1SNA 399 067	R0600		
Orange	 D 2,5/5.I.3L	1SNA 399 260	R2000		
Yellow	 D 2,5/5.I.3L	1SNA 400 219	R1100		

Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
With isolated ferrule	Rigid	0,12-4* mm ²	26-12 AWG	26-12 AWG
	Flexible	0,12-2,5 mm ²	26-12 AWG	26-12 AWG


Voltage			
Rated	800 V	600 V	600 V
Impulse withstand	8 kV		
Pollution degree	3		

Current			
Rated	24 A	20 A	20 A










Wire size			
Rated / Gauge	2,5 mm ² /A2	12 AWG	12 AWG
Wire strip. length	Recomm. screwdriver	Weight	Protection
9,5 mm	3,5 mm	8 g	IP20
.37"	.14"	.28 oz	NEMA 1

D 2,5/5.I.4L

Spacing 5 mm +0,05 (.198")



4 springs + 1 test.

				
Color	Type	Part number		
Grey	 D 2,5/5.I.4L	1SNA 399 071	R0200	
Blue	 D 2,5/5.I.N.4L	1SNA 399 070	R1500	
Orange	 D 2,5/5.I.4L	1SNA 399 270	R2200	
Yellow	 D 2,5/5.I.4L	1SNA 400 220	R1600	

Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
With isolated ferrule	Rigid	0,12-4* mm ²	26-12 AWG	26-12 AWG
	Flexible	0,12-2,5 mm ²	26-12 AWG	26-12 AWG

Voltage			
Rated	800 V	600 V	600 V
Impulse withstand	8 kV		
Pollution degree	3		

Current			
Rated	24 A	20 A	20 A

Wire size			
Rated/gauge	2,5 mm ² /A2	12 AWG	12 AWG
Wire strip. length	Recomm. screwdriver	Weight	Protection
9,5 mm	3,5 mm	9 g	IP20
.37"	.14"	.32 oz	NEMA 1

Type	Part number		
FED5.I.3L V0	th. 2,5 mm	1SNA 290 311	R0600
FED5.I.3L V0	th. 2,5 mm	1SNA 290 314	R0100
FC2.MC	DIA 2,0 mm	1SNA 107 239	R0300
BJDL5.2 V0	2 poles	1SNA 291 102	R2300
BJDL5.3 V0	3 poles	1SNA 291 103	R2400
BJDL5.4 V0	4 poles	1SNA 291 104	R2500
BJDL5.5 V0	5 poles	1SNA 291 105	R2600
BJDL5.6 V0	6 poles	1SNA 291 106	R2700
BJDL5.7 V0	7 poles	1SNA 291 107	R2000
BJDL5.8 V0	8 poles	1SNA 291 108	R0100
BJDL5.9 V0	9 poles	1SNA 291 109	R0200
BJDL5.10 V0	10 poles	1SNA 291 110	R2600
CBD5.2L	th. 0,5 mm	1SNA 291 077	R2400

Type	Part number		
FED5.I.3L V0	th. 2,5 mm	1SNA 290 311	R0600
FED5.I.3L V0	th. 2,5 mm	1SNA 290 314	R0100
FC2.MC	DIA 2,0 mm	1SNA 107 239	R0300
CBD5.2L	th. 0,5 mm	1SNA 291 077	R2400

On top : RC 510 or RPC

On top : RC 510 or RPC