



# Xitanium/Fortimo LED Drivers indoor dimmable

Xitanium 25W 0.3-1A 36V TD/Is 230V

Xitanium and Fortimo LED drivers are specially designed to operate LED solutions for general lighting applications such as downlighting, spot/accent lighting and linear lighting. Flexibility in luminaire design is assured thanks to an adjustable output current (AOC) and, in most independent versions, a new modern 3-in-1 housing design. The adjustable output current enables operation of various LED configurations from different LED manufacturers, as well as ensuring the solution can accommodate new LED generations – making it “future-proof”. There are special dimmable versions which enable the use of lighting controls for further energy savings.

## Product data

### • Product Data

Order code	914351 00
Full product code	872790091435100
Full product name	Xtitanium 25W 0.3-1A 36V TD/Is 230V
Order product name	Xtitanium 25W 0.3-1A 36V TD/Is 230V
Pieces per pack	1
Packing configuration	10
Packs per outerbox	10
Bar code on pack - EAN1	8727900914351
Bar code on outerbox - EAN3	8727900914351
Logistic code(s) - 12NC	929000485803
Net weight per piece	0.140 kg

Output Current Range (mA)	300-1000
Total Harmonic Distortion IEC	20 %
Dimming range	100-10 %
Inrush Current Peak	16 A
Type of Dimming	Touch&DALI

### • Wiring Characteristics

Connection on driver to L2	JST connector
Hot wiring	Yes

### • Temperature Characteristics

T-case maximum	90 C
T-ambient	-20 (min), 60 (max) C

### • General Characteristics

Relative Humidity	95 -
IP Classification	20
Average Lifetime 10% Failure	50000 hr
System Description	TD/Is [Dimmable Independent Small]
Number of LEDs	6 (min), 9 (max) x

### • Approval&Application Char's

Isolation classification	SELV
--------------------------	------


### • Product Dimensions

Length A1	150 mm
Length A2	125 mm
Length A3	114 mm
Length A4	108 mm
Width B1	46 mm
Height C1	32 mm
Screw Hole Diameter D1	4.2 mm


### • Operating Characteristics

12V output	No
Ripple current	20 %
Efficiency Range	85-87 %
Power Factor Range	0.9-0.95
Input Power max	15-30 W
Output Voltage Range	18-36 V

## Dimensional drawing




Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	A4 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
Xtitanium 25W 0.3-1A 36V TD/Is 230V	150	125	114	108	46	32	4.2



Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	A4 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
Xtitanium 25W 0.3-1A 36V TD/Is 230V	150	125	114	108	46	32	4.2

## Dimensional drawing



Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	A4 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
Xitanium 25W 0.3-1A 36V TD/ls 230V	150	125	114	108	46	32	4.2



© 2011 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2011, January 11  
data subject to change