

Datasheet

RS Pro 7A T Non-Resettable Surface Mount Fuse, 63 V ac/dc

RS Stock No: **764-9396**



Product Details

RS Pro 7 A T non-resettable surface mount fuse has a voltage rating of 63 V ac/dc. This fuse provides considerable space and time saving features for low voltage applications. It is suitable for protection of high value silicon ICs like alarm systems, audio/visual equipment, computer boards, portable telephones, power supplies and medical apparatus.

Features and Benefits

- Surface mount technology
- Offers considerable space and time saving features for low voltage applications
- Perfect for protection of high value silicon ICs such as alarm systems, audio/visual equipment, computer boards, portable telephones, power supplies and medical apparatus

**Specifications:**

| | |
|---|-----------------------|
| Body Material | FR4 Board |
| Breaking Capacity (at Maximum Voltage Rating) | 100 A at 63 V ac/dc |
| Current Rating | 7 A |
| Dimensions | 3.1 x 1.6 x 0.7 mm |
| Fuse Speed | T |
| Height | 0.7 mm |
| Length | 3.1 mm |
| Maximum Operating Temperature | +125°C |
| Minimum Operating Temperature | -55°C |
| Operating Temperature Range | -55 to +125°C |
| Terminal Material | Copper, Tin |
| Voltage Rating | 63 V ac/dc |
| Width | 1.6 mm |
| Standards Met | cURus; RoHS Compliant |