







PART NO.	ENG. NO.	
02-06-2131	1854-(901)	
02-06-2132	1854-(901)L	
02-06-2134	1854-(901)1	OBSOLETE
02-06-6137	1854-(591)	
02-06-6136	1854-(591)L	
02-06-6138	1854-(561)	
02-06-6139	1854-(561)L	
02-06-6130	1854-(550)	
02-06-6135	1854-(550)L	
02-06-6143	1854-(228)	
02-06-6144	1854-(228)L	
02-06-6145	1854-(603)1	OBSOLETE




SECT. "B-B"
SCALE:10X



SECT. "C-C"
SCALE:10X



SECT. "A-A"



LEGEND

1854-(****)*

P=PREPLATE
BLANK=POSTPLATE

FINISH CODE

FORM
BLANK=CHAIN
1=CHAIN WITH INTERLEAF
PAPER ON REEL,
L=LOOSE

NOTES:

1. MATERIAL: BRASS

2. FINISHES:

901 HOT TIN DIP (.00051)/.000020 MIN.

* 228 SELECT GOLD PLATE (.00075)/.000030 MIN. IN CONTACT AREA, SELECT TIN (.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL, WITH (.000010)/.000025 MAX. SELECT GOLD FLASH AS INDICATED.

561 SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA, (.00127)/.000050 MIN. NICKEL OVERALL.

591 SELECT GOLD PLATE (.00127)/.000050 MIN. IN CONTACT AREA, OVER (.00127)/.000050 MIN. NICKEL OVERALL WITH (.00025)/.000010 MAX. GOLD FLASH OVERALL.

550 SELECT GOLD PLATE (.00038)/.000015 MIN. IN CONTACT AREA, OVER (.00076)/.000030 MIN. NICKEL OVERALL WITH (.00025)/.000010 MAX. GOLD FLASH OVERALL.

* THE PRIMARY SHIPPING CARTON WILL BE LABELED, "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC", CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD.

3. PRODUCT SPECIFICATIONS: PS-02-06

4. PACKAGING INFORMATION: NOT AVAILABLE

5. TERMINAL FOR USE WITH (1,57)/.062 DIA. SERIES HOUSINGS AND WILL ACCEPT 24 THRU 30 AWG. WIRE WITH (1,02/2,29)/.040/0.090 INSULATION DIA.

WORK AREA
PLOT

SEE REVISION BLOCK
EC NO: UPC2004-2097
DRAWN: RHOLTS 04/27/2004
CHKD:
APPR:

QUALITY SYMBOLS
DESCRIPTION
REV

GENERAL TOLERANCES (UNLESS SPECIFIED)
DIMENSION STYLE
INCH/MM
DRAWN BY
GEP
DATE
9/27/87
CHECKED BY
RW
DATE
9/27/87
APPROVED BY
RAS
DATE
9/27/87
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

SCALE
8:1
DESIGN UNITS
INCH
THIRD ANGLE PROJECTION
TITLE
CRIMP TERMINAL, MALE
(1,57)/.062 DIA., BRASS
FOR 24 THRU 30 GA. WIRE
MOLEX INCORPORATED
MATERIAL NO.
SEE CHART
DOCUMENT NO.
SD-1854*
SHEET NO.
1 OF 1

REVISIONS
AP REMV Sn/Pb PLATING REDRAWN TO ME10 UCP2004-2097 RHOLTS 5/07/04
AN OBSOLETE P/N UCR2002-0270 COMERC 01/9/27
AM2 OBSOLETE -675 & -575L ECR U6 0358 9/15/95 RW
AM1 ADD -(603)1 PER ERO #30605 11-5-90 RW
AM REV. & REDRAWN PER ECR 10372 SEP 9-21-87 RW