



MASTER LEDspot PAR - elegance meets efficiency

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.

Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of 50 W and 75 W halogen lamps, MASTER LEDspot PAR 20 (dimmable), PAR 38 and PAR 30 deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today.

The product is free of mercury and other hazardous materials.

Product Benefits

- Up to 80% energy saving compared to halogen lamps
- Retrofittable and compatible with existing fixtures with E27 holder
- Lower maintenance costs

Product Features

- Lifetime of 45,000 hours
- Dimmable (except PAR38 OD)
- UV- and IR-free light for less heat and protection for heat-sensitive objects
- Free of mercury and hazardous materials


Applications

- Especially suitable for public areas like lobbies, corridors, stairwells and restaurants/bars

Product Range



Dimension Drawing



Technical Specification

Type	Wattage \cong replaces (W)	Voltage (V)	Cap-Base	Bulb	Correlated Colour Temperature (K)	Colour Rendering Index (Ra)	\angle (°)	Luminous Flux (lm)	Luminous Intensity (cd)	Dim-mable	Photo letter	Dim. no.	Polar intensity diagram	Ordering number 8718291...
MASTER LEDspot	9.5 \cong 75	220-240	ES	PAR30S	2,700	80	25	650	3,500	Yes	A	1	P1	71434700
MASTER LEDspot	9.5 \cong 75	220-240	ES	PAR30S	4,000	80	25	750	3,850	Yes	A	1	P2	71436100
MASTER LEDspot	14.5	220-240	ES	PAR38	2,700	80	25	900	4,700	Yes	B	2	P3	71438500
MASTER LEDspot	17	230	ES	PAR38	2,700	80	25		3,500	No	C	3	P4	11931900