







LOC	DIST	REVISIONS			
CM	00	P	LTR	DESCRIPTION	DATE
		L		ECO-06-016113	17JUL06

1. WIRE RANGE: 0.13 — 0.35 mm² (26-22 AWG) .
2. INSULATION RANGE: 0.89 — 1.65 [.035 — .065] DIA.
LARGER SIZES OF 1.68 — 1.91 [.066 — .075] DIA
INSULATION REQUIRES WIRE AND CRIMP EVALUATION
FROM AMP INCORPORATED.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 0.00076 [.000030] MIN THK GOLD STRIPES IN LOCALIZED
PLATE AREA ON BEAM AND DIMPLE OVER 0.00127 [.000050]
MIN THK NICKEL OVER ENTIRE CONTACT.
- 5 AFTER PACKAGING AND SHIPMENT, A LANCE HEIGHT
0.46 — 0.71 [.018 — .030] IS PERMISSABLE.
- 6 PRE-TIN MAY OR MAY NOT HAVE NICKEL UNDERPLATE.



SECTION A-A
SCALE 20:1

SECTION B-B
SCALE 20:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	17FEB05	tyco Electronics		Tyco Electronics Corporation Harriaburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK D. BOSSI	17FEB05	APVD D. BOSSI		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC		RESTRICTED TO	
0 PLC ± -		1 PLC ± -		2 PLC ± -		3 PLC ± 0.13 [.005]	
4 PLC ± -		ANGLES		FINISH		SEE TABLE	
MATERIAL 0.198 PH BRZ		WEIGHT		A1 00779		C=770601	
CUSTOMER DRAWING		SCALE		10:1		SHEET	
				1		OF 1	
						REV	
						L	