

Product-type designation

SCALANCE X206-1LD



SCALANCE X206-1LD, MANAGED IE SWITCH,
6 X 10/100MBIT/S RJ45 PORTS,
1 X 100MBIT/S SINGLEMODE BFOC,
ERROR SIGNAL CONTACT WITH SET BUTTON,
REDUNDANT POWER SUPPLY, PROFINET-IO DEVICE,
NETWORK MANAGEMENT,
INTEGRATED REDUNDANCY MANAGER,
INCL. ELECTRONIC MANUAL ON CD,
C-PLUG OPTIONAL

Transmission rate

Transfer rate / 1	10 Mbit/s
Transfer rate / 2	100 Mbit/s

Interfaces

Number of electrical/optical connections	
• for network components or terminal equipment / maximum	7
Number of electrical connections	
• for network components and terminal equipment	6
• for alarm contact	1
• for power supply	1
• for redundant power supply	1
Design of electrical connection	
• for network components and terminal equipment	RJ45 port
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
Number of optical interfaces / for optical waveguide / at 100 Mbit/s	1
Design of optical interface / for optical waveguide / at 100 Mbit/s	BFOC port (singlemode up to 26 km)
Connectable optical power relative to 1 mW	
• of the transmitter output	-15 ... -7 dB
Optical sensitivity relative to 1 mW / of the receiver input / minimum	-34 dB

Attenuation / of fiber-optic cable transmission link / minimum necessary	0 dB
Range / at the optical interface / depending on the optical fiber used	0 ... 26 km
design of the removable storage / C-PLUG	Yes
Inputs/outputs	
Operating voltage / of signaling contacts / at DC / rated value	24 V
Operating current / of signaling contacts / at DC / maximum	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of supply voltage	DC
Supply voltage / external	24 V
• minimum	18 V
• maximum	32 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.2 A
Active power loss / at 24 V / for DC	5.28 W
Permitted ambient conditions	
Ambient temperature	
• during operating	-40 ... +60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Relative humidity / at 25 °C / without condensation / during operating / maximum	95 %
Protection class IP	IP30
Design, dimensions and weight	
Design	compact
Width	60 mm
Height	125 mm
Depth	124 mm
Net weight	0.78 kg
Type of mounting	
• 35 mm DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
Product properties, functions, components / general	
Cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	50
Cascading in cases of star structuring	Any (depending only on signal propagation time)
Product function	
• CLI	Yes
• web-based management	Yes

• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• Port mirroring	Yes
• for IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• DCP	Yes
• LLDP	Yes
Identification & maintenance	
• I&M0 - device-specific information	Yes
• I&M1 - plant identification/location name	Yes
Product functions / Diagnosis	
Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
Product functions / DHCP	
Product function / DHCP client	Yes
Product functions / Redundancy	
Product function	
• Ring redundancy	Yes
• Redundancy manager	Yes
• Standby redundancy	No
• HSR redundancy protocol	Yes
• MRP redundancy protocol	Yes
• redundancy procedure PRP	No
• Passive listening	Yes

Protocol / is supported / PRP	Yes
Product functions / Security	
Protocol / is supported / SSH	Yes
Product functions / Time	
Product function / SICLOCK support	Yes
Protocol / is supported	
• NTP	No
• SNTP	Yes
Standards, specifications, approvals	
Standard	
• for EMC / from FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
• for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for safety / of CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for hazardous area / of CSA and UL	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2
Verification of suitability	EN 61000-6-2, EN 61000-6-4
• CE mark	Yes
• C-Tick	Yes
• KC approval	Yes
• Railway application in accordance with EN 50155	No
• Railway application in accordance with EN 50124-1	No
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	Yes
• Germanische Lloyd (GL)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	Yes
letzte Änderung:	May 14, 2012