

## LC2DT40BD

TeSys D changeover contactor - 4P(4 NO) - AC-1 -  
≤ 440 V 40 A - 24 V DC coil



### Main

Range	TeSys
Product name	TeSys D
Product or component type	Changeover contactor
Device short name	LC2D
Contactor application	Resistive load
Utilisation category	AC-1
Device presentation	Preassembled with reversing power busbar
Poles description	4P
Pole contact composition	4 NO
[Ue] rated operational voltage	≤ 690 V AC 25...400 Hz for power circuit ≤ 300 V DC for power circuit
[Ie] rated operational current	40 A (≤ 60 °C) at ≤ 440 V AC AC-1 for power circuit
Control circuit type	DC standard
Control circuit voltage	24 V DC
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Overvoltage category	III
[Ith] conventional free air thermal current	40 A at ≤ 60 °C for power circuit 10 A at ≤ 60 °C for signalling circuit
Irms rated making capacity	450 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated breaking capacity	450 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	120 A ≤ 40 °C 1 min power circuit 240 A ≤ 40 °C 10 s power circuit 380 A ≤ 40 °C 1 s power circuit 50 A ≤ 40 °C 10 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit
Associated fuse rating	40 A gG at ≤ 690 V coordination type 2 for power circuit 63 A gG at ≤ 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1
Average impedance	2 mOhm at 50 Hz - Ith 40 A for power circuit
[Ui] rated insulation voltage	600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL
Electrical durability	1.4 Mcycles 40 A AC-1 at Ue ≤ 440 V
Power dissipation per pole	3.2 W AC-1
Protective cover	With

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Interlocking type	Mechanical
Mounting support	Plate Rail
Standards	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14
Product certifications	BV CCC CSA DNV GL GOST RINA UL LROS
Connections - terminals	Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : connector 1 cable(s) 2.5...10 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : connector 2 cable(s) 2.5...10 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : connector 1 cable(s) 2.5...10 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : connector 2 cable(s) 2.5...10 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 2.5...16 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : connector 2 cable(s) 2.5...16 mm <sup>2</sup> - cable stiffness: solid - without cable end
Tightening torque	Control circuit : 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit : 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit : 1.7 N.m - on connector - with screwdriver flat Ø 6 mm Power circuit : 1.7 N.m - on connector - with screwdriver Philips No 2
Operating time	53.55...72.45 ms closing 16...24 ms opening
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	30 Mcycles
Operating rate	3600 cyc/h at ≤ 60 °C

## Complementary

Coil technology	Built-in bidirectional peak limiting diode suppressor
Control circuit voltage limits	0.1...0.25 U <sub>c</sub> at 60 °C drop-out 0.7...1.25 U <sub>c</sub> at 60 °C operational
Time constant	28 ms
Inrush power in W	5.4 W at 20 °C
Hold-in power consumption in W	5.4 W at 20 °C
Auxiliary contacts type	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1

Type mirror contact (1 NC) conforming to IEC 60947-4-1

Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non-overlap time	1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)
Insulation resistance	> 10 MOhm for signalling circuit

## Environment

IP degree of protection	IP2x front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C at U <sub>c</sub>
Operating altitude	3000 m without derating in temperature
Fire resistance	850 °C conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 8 Gn for 11 ms
Height	91 mm
Width	90 mm
Depth	98 mm
Product weight	0.85 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0711 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations